






Electrical Test:

1. 100%Test(Open ,short ,miss wire)
2. Contact Resistance: 2 ohm max.
3. Insulation Resistance: 10M ohm Min.
4. Hi-Pot: 300VDC/10ms.



Pin Assignment



①	A0020100-00174	USB TYPE C~n Back Nickel Plated Shell	1	pcs
⑩	A0020100-00175	USB TYPE C~n Front Nickel Plated Shell~	1	pcs
⑨	A10-R042106	Copper Foil:W=5MM 25u	0.012	M
⑧	A10-R075552	H.S TUBE Color:Black Ø:1.0 L=16mm*1pcs	0.016	M
⑦	A5-R047001	Transparent PE	16	g
⑥	A5-R047011	45P PVC Color: BLACK	6	g
⑤	B010-00880	USB 2.0 C Type Black Insulation Nickel Plated Shell With PCBA(Resistance10KΩ)	1	pcs
④	A6-R107047	USB2.0 AM Front Shell Nickel Plated Shell (L=26.14MM)	1	pcs
③	A6-R107048	USB2.0 AM Back Shell Nickel Plated Shell (OD:3.5~4.5mm)	1	pcs
②	A2-R029131	USB2.0 AM White Insulation Solder Type,G/F Plated Terminal	1	pcs
①	A4-R003744	NO UL 26AWG(19/0.1TC)*2C+20AWG(30/0.165TC+250Dnylon)*1C+EAB(16/8/0.08TC 90%TC) OD:4.2MM BLACK NO MARK	3.0	M
NO		DESCRIPTION	Q'TY	UNIT

REV.	ECN	DESCRIPTION	DATE	NAME
TOLERANCE INCHES M/M				
. X	. 015	. 30		
. XX	. 010	. 10		
. XXX	. 005	. 05		
DRAWN BY		李敏		
CHECK BY				
APPD BY				
SCALE		NONE		
UNIT		mm		
DATE		2015.05.13		
CUSTOMER :		CPC		
CUSTOMER P/N :		CS28710		
DRAWING NO. :		C06026-00003		
REV.		A01		