



Speed, Performance, Value - Perfect Balance

- 9 weighing units
- Full range tare
- Zero Tracking
- Simple 4 button operation
- Backlit LCD display
- Stainless steel pan
- ShockProtect™ overload three-point protection
- Can be stacked for storage (120mm pan size only)
- Lock down mounting slot for Kensington® type lock and cable
- Dual tare keys
- Lightweight and portable
- Modern low profile design
- Colour coded, sealed keypad
- Low cost and simple to use
- External calibration
- Battery power (6 x AA Batteries)
- Auto sleep / power down function to save battery life
- AC Adapter
- Weighing
- Below balance weighing
- Weight accumulation



Technical Specifications

Model	CQT 202	CQT 251	CQT 601	CQT 1501	CQT 2601	CQT 2000	CQT 5000
Maximum capacity	200g	250g	600g	1500g	2600g	2000g	5000g
Readability	0.01g	0.1g	0.1g	0.1g	0.1g	1g	1g
Repeatability (S.D.)	0.02g	0.1g	0.1g	0.1g	0.1g	1g	1g
Linearity (\pm)	0.02g	0.1g	0.1g	0.2g	0.2g	1g	1g
Typical stabilisation time	3 Sec	2 Sec		3 Sec			2 Sec
Draught shield dimensions	130 x 90mm				-		
Pan size	4.7" & Oslash; / 120mm & Oslash; ;				5.7" & Oslash; / 145mm & Oslash; ;		

General Specifications

Units of measurement	Kilogram (kg), Gram (g), Pound (lb), Ounce (Oz), Carat (ct), Dram (d), Grain (GN), Newton (N), Taels T. (TL.T)
Power supply	12VAC 150mA adapter or 6 x AA batteries
Overall dimensions (wxdxh)	6.8 x 10 x 3.4" / 173 x 255 x 86mm

Key Accessories

- Security Lock and Cable
- Hard Carry Case with Lock
- In-use Cover
- ASTM 2 - 1000g calibration weight
- ASTM 2 - 100g calibration weight
- ASTM 3 - 200g calibration weight
- ASTM 4 - 2000g calibration weight



Adam Equipment - offices worldwide

www.adamequipment.com