

3-Phase/Motor Rotation Testers



▶ 61-521
3-Phase
sequence and
motor rotation



▶ 61-520
3-Phase
sequence

61-521 FEATURES

- Identifies three-phase sequence
 - Indicates motor rotation
 - Checks for open phases
 - For use up to 600V
 - 2-year warranty
- Includes carrying case

61-520 FEATURES

- For use up to 600V
 - Color-coded insulators over alligator clips
 - Shock resistant housing
 - Easy to read
 - 2-year warranty
- Includes carrying case



Specifications		61-681
	RANGE & RESOLUTION	ACCURACY
FOOT CANDLES	20.00/200.00/2000.0/200000	2%
LUX	20.00/200.00/2000.0/200000	2%



▶ 61-681

Digital Light Meter

FEATURES

- Wide lighting range
 - Foot candle and lux measurement
 - Remote light sensor
 - Cosine and color corrected
 - Peak hold
 - Low battery indication
 - 2-year warranty
- Includes carrying case

Infrared Thermometer

Specifications		61-682
	RANGE & RESOLUTION	ACCURACY
	0° F to 500° F (-18° C to 260° C)	3.0%



▶ 61-682

FEATURES

- 15:1 angle of viewability
 - Built-in laser pointer
 - Backlit display
 - Auto power off
 - Measures temperature from 0° F to 500° F (-18° C to 260° C)
 - 2-year warranty
- Includes carrying case