# Product data sheet Characteristics

# ABE7H16R11 WIR BAS 16IO LED 1B-1LEV

#### Certifications and standards

Product certifications

BV CSA

Det Norske Veritas

GL

Lloyd s Register of Shipping

UL

#### Connections

Connections - terminals	Screw type terminals 1 0.14 - 2.5 mm² 2614 flexible without cable end Screw type terminals 1 0.09 - 1.5 mm² 2816 flexible with cable end Screw type terminals 1 0.14 - 2.5 mm² 2612 solid Screw type terminals 2 0.09 - 0.75 mm² 2820 flexible with cable end Screw type terminals 2 0.2 - 2.5 mm² 2414 solid
Connector type	HE-10
Pin number	20

#### Electrical

[Ui] rated insulation voltage	2000 V	
[Us] rated supply voltage	1930 V IEC 61131-2	
Current per channel	<=0.5 A	
Current per output common	<=1.8 A	
Polarity distribution	No	
Short circuit protection	2 A internal fuse 5 x 20 mm fast blow PLC end	
Supply circuit type	DC	
Supply current	<=1.8 A	
Voltage drop on power supply fuse	0.3 V	

#### Environment

IP degree of protection	IP2x IEC 60529
Ambient air temperature for operation	-5 - 60 °C IEC 61131-2
Ambient air temperature for storage	-40 - 80 °C IEC 61131-2
Pollution degree	2 IEC 60664-1
Protective treatment	TC
Resistance to electrostatic discharge	8 kV air level 3 IEC 61000-4-2 4 kV contact level 3 IEC 61000-4-2
Resistance to fast transients	2 kV level 3 IEC 61000-4-4
Resistance to incandescent wire	750 °C < 30 s IEC 60695-2-11
Resistance to radiated fields	10 V/m level 3 26000000 - 1000000000 Hz IEC 61000-4-3
Shock resistance	15 gn 11 ms IEC 60068-2-27
Vibration resistance	2 gn IEC 60068-2-6 10 - 150 Hz

_							
-	ш	n	C:I	н.	$\sim$	n	а

Number of terminal per channel	1
Status LED	1 LED per channel green channel status 1 LED green power ON

#### Installation

Fixing mode	By clips 35 mm symmetrical DIN rail By screws solid plate with fixing kit
Installation category	II IEC 60664-1

# Physical characteristics

Number of horizontal rows	1
Product weight	0.274 kg
Tightening torque	0.6 N.m flat Ø 3.5 mm
Width	125 mm

#### Product identification

Number of channels	16	
Product or component type	Passive discrete I/O sub-base	
Range of product	Advantys Telefast ABE7	
Sub-base type	I/O sub-base	

### Complementary description

Long description	WIR BAS 16IO LED 1B/1LEV
------------------	--------------------------

#### Main characteristics

Brand	Telemecanique
Commercial Reference field	ABE7H16R11
Common description	WIR BAS 16IO LED 1B/1LEV
Current cross distribution chain status	08 - Commercialised
EAN Number	3389110544947
Short description	WIR BAS 16IO LED 1B-1LEV

# Logistic

Basic packaging quantity	1
Minimum sales order quantity	1

# Management information

Effect. date next global CDC	96/01/25
Product part number	ABE7H16R11

#### Reporting

Department code	Low End Control
Domain	AUTOMATION
Internal Domain Code	AC
Product Line	ILEC0
Strategic Product Family	TBD

#### Weight and dimensions

First packaging gross height	0.067 m
First packaging gross weight	0.277 kg
First packaging gross width	0.08 m
First packaginggross length	0.14 m