



**IP21**  
 SUITABILITY

**Circuit Guard® Automatic Set  
 Portable GFCI Line Cords**



**GFP4C15A**

Description	Catalog Number
18" (45.7 cm) GFCI line cord.	<b>GFP4C15A</b>
6' (182.9 cm) GFCI line cord.	<b>GFP6C15A</b>
25' (762.0 cm) GFCI line cord.	<b>GFP25C15A</b>
15' (457.2 cm) GFCI power supply cord with stripped leads.	<b>GFPOEMA*</b>

**Circuit Guard® Manual Set  
 Portable GFCI Line Cords**



**GFP25C15A**

Description	15A 120V AC	20A 120V AC
18" (45.7 cm) GFCI line cord.	<b>GFP4C15M</b>	-
3' (91.4 cm) GFCI line cord.	-	<b>GFP3C20M</b>
6' (182.9 cm) GFCI line cord.	<b>GFP6C15M</b>	-
25' (762.0 cm) GFCI line cord.	<b>GFP25C15M</b>	-
15' (457.2 cm) GFCI power supply cord with stripped leads.	<b>GFPOEMM*</b>	-
50' (1524.0 cm) GFCI power supply with Elastogrip® watertight straight blade.	<b>GFP50C15WM</b>	-
100' (3048.0 cm) GFCI power supply with Elastogrip® watertight straight blade.	<b>GFP100C15WM</b>	-

Note: \*Total length is 15' 4.5" (468.6 cm) including leads: green 4.5" (114.3), black and white 3.5" (88.9). Each pre-stripped .375" (9.5).

**Circuit Guard® Manual Set  
 Twist-Lock Portable GFCI Line Cords**



**GFP6C15M**

Description	15A 120V AC	20A 120V AC
3' (91.4 cm) GFCI line cord.	<b>GFP3C15MTL</b>	<b>GFP3C20MTL</b>

**Automatic Set GFCI**

Automatically energizes or sets the GFCI for use upon plug in and after the loss of primary power (power failure or unplugging the device). After a ground fault condition, unit must be reset by pushing the reset button. This feature eliminates the need for unit to be reset each time it is plugged in or powered up. Ideal for equipment intended for continuous use where a temporary power failure is likely and undesirable. Examples are pumps, pressure washers, portable signs or lighting and engine heaters.

**Manual Set GFCI**

Requires the GFCI to be manually set for use by pressing the reset button upon plug in and after loss of primary power (power failure or unplugging the device). Must be manually reset after a ground fault condition. Ideal for applications where operator injury might occur if equipment were to restart after a power failure. Typical equipment includes power drills, saws, lathes and grinders.



**GFPOEMM**

	Straight Blade	Twist-Lock®
Input	15A NEMA 5-15P, 20A NEMA 5-20P.	15A NEMA L5-15P HBL47CM20C, 20A NEMA L5-20P HBL23CM11.
Output	15A NEMA 5-15R (except GFPOEMM), 20A NEMA 5-20R.	15A NEMA L5-15R HBL47CM29C, 20A NEMA L5-20R HBL23CM13.

**Specifications**

**Portable GFCI Line Cords**

Trip Level	4 to 6 mA.
Trip Time	.025 sec. nominal.
Frequency	60 Hz.
Voltage	120V AC +10% – 15%. Incorporates no voltage release feature.
Amperage	15A/20A.
Maximum Interrupting Capacity	2000A.
Operating Temperature	-35°C to 66°C or -30°F to 150°F.
Maximum Humidity	95%.
Housing	High-impact, UV stabilized PVC. UL 94V-0 flammability classification. Meets UL and CSA watertight requirements. Adhesive bonded.
Cord Type	14/3 SJTW-A (UL), SJTW (CSA). Except GFP3C20M, GFP3C15MTL and GFP3C20MTL are 12/3 SJTW.
Visual Fault Indication Light On	Indicates fault.
Listing and Standards	Meets UL943 Class A, UL File E41978, CSA Certified.
Codes	Meets all NEC® and CEC requirements.

NEC® is a registered trademark of the National Fire Protection Association (NFPA).



**GFP3C20MTL**