

## Standard Polyester Expandable Braided Sleeving

Polyester expandable sleeving is standard flame-retardant. It offers durable abrasion resistance in a wide range of industrial applications. The open weave construction allows an easy installation on a bundle of hoses and cables, even if some with bulky or large connectors. Totally expanded the sleeving can reach at least 1.5 times than the initial dimension.



### Application

It mainly used to cover cables, wire harnesses, tubes, industrial hoses where is required a good mechanical protection.

Can be sold in Dispensor Box, 10m/box

### Datasheet

Nominal size (W)		Expandable range		Packing (L)
Inch	mm	Min. ( I )	Max. ( O )	Standard spool
1/8"	3	1	6	1000 m
1/4"	6	3	9	500 m
5/16"	8	5	16	350 m
3/8"	10	7	19	350 m
1/2"	12	8	24	300 m
5/8"	16	10	27	250 m
3/4"	19	14	30	200 m
1"	25	18	35	200 m
1 1/4"	32	20	50	150 m
1 1/2"	40	30	60	100 m
1 3/4"	45	35	75	100 m

2"	50	40	80	100 m
2 1/2"	64	45	105	100 m
3"	76	64	120	100 m

### Technology Index—Standard (BSFR-)

Material	Polyester-Standard
Operating Temperature	-50°C-+150°C
Melt point	240±10°C
Flammability	VW-1
Standard color	Black and grey
Other colors	Red, blue white etc.
Approval	UL, ,ROHS
Cutting tool	Hot knife