



GFP315A

Circuit Guard® Plug-In Portable GFCI

Description	Rating	Catalog Number
Three outlet plug-in.	15A, 120V AC	GFP315A

Specifications

GFP315A		
Trip Level	4 to 6 mA.	
Trip Time	.025 sec. nominal.	
Frequency	60 Hz.	
Voltage	120V AC +10% – 15%. Incorporates no voltage release feature.	
Amperage	15A.	
Maximum Interrupting Capacity	2000A.	
Operating Temperature	-35°C to 66°C or -30°F to 150°F.	
Maximum Humidity	95%.	
Housing	High-impact ABS.	
Input	NEMA 5-15P.	
Output	3 NEMA 5-15R.	
Fault Indication	Indicator light.	
Center Screw	For optional permanent mounting.	
Listings and Standards	Meets UL498 for receptacles, UL943 Class A for GFCIs UL File E41978, CSA Certified.	
Codes	Meets all NEC® and CEC requirements.	

GFCI Tester

Description	Rating	Catalog Number
Ground fault tester.	120V AC	GFT2G



GFT2G

- Designed to measure the trip level of portable or “wired-in” GFCI’s in a range of 2-7mA. Leakage level can be adjusted from 2-7mA.
- Ideal for measuring leakage level of GFCI breakers, GFCI portables and GFCI receptacles.

Dimensions

