

48-Port Serial Console/Terminal Server

MODEL NUMBER: **B096-048**



Description

Tripp Lite's B096-048 is the most advanced console / terminal server platform available today. In one secure, 1U rackmountable appliance, it offers an in-band and out-of-band management solution for serial console ports, servers, virtual servers, service processors, UPS & PDU's, environmental monitoring. This 48 port serial console / terminal server enables system administrators to securely access and control their data centers and networks from anywhere in the world. Supports 3G cellular out-of-band access. The USB port on the console server is compatible with the Pantech ULM290 VZW and the following Sierra Wireless USB modems; Compass 888, USB 598, USB 598U, USB 312U, USB 308, and U313. And this enterprise level unit is equipped with a built in modem, dual Ethernet, dual AC power, 16GB USB flash and runs on Linux for scalability and reduced downtime.

The B096-048 offers advanced software features that surpass the requirements of even the most demanding applications. These features include Network UPS Tools for UPS monitoring, PowerMan for integrated PDU and RPC functions with in session hotkey support, Pattern match alerting, Open access to the Linux shell for scripting, heartbeat monitoring with automatic failover, Cisco pinouts and much more. Available in 16 and 48 port models, the B096 family of Console Servers are the perfect fit for in or out of band access to vital IT assets.

Made in the USA. Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases.

Features

- Built in modem for out-of-band dial-in access
- Configured to use standard Cat5e/6 patch cable when connecting to Cisco devices
- Tripp Lite's console servers all use an embedded FIPS 140-2 OpenSSL cryptographic module that has been validated to meet the FIPS 140-2 standards and has received Certificate #1051.
- When using SSH, HTTPS or SDT Connector to connect to any service on the console server while running in FIPS mode, they will be utilizing the embedded FIPS compliant module. In order to connect using any of the protocols, you must use a cryptographic algorithm that is FIPS approved or it will fail.
- Supports 3G cellular out-of-band access. The USB port on the console server is compatible with the Pantech ULM290 VZW and the following Sierra

Highlights

- Dual Ethernet, Dual Power Supply, and Built-In Modem
- Secure in-band and out-of-band access
- Supports 3G cellular out-of-band access
- Features 16GB Internal USB Flash
- 1U rackmountable
- Configured to use standard Cat5e/6 patch cable when connecting to Cisco devices
- Validated to meet FIPS 140-2 standards
- Manage all equipment in the rack: servers, UPS, routers, switches, etc
- LINUX with source code access allows custom scripts
- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases
- Made in the USA

Package Includes

- B096-048, 48-Port Serial Console / Terminal Server
- Rackmount hardware
- 2 x 6-ft, Cat5e Patch cables
- 1 x DB9F - RJ45 Crossover Adapter
- 1 x DB9F - RJ45 Straight-Through Adapter
- 2 x 6-ft, 5-15P to C13 Power cable



Wireless USB modems; Compass 888, USB 598, USB 598U, USB 312U, USB 308, and U313.

- 16GB local FTP/TFTP storage for device configuration files
- IPsec VPN support
- Secure Shell (SSH V2 and V3)
- TACACS+ , RADIUS, LDAP and Kerberos authentication
- PAP/CHAP authentication (dial up)
- Local authentication
- System event syslog
- SSH port and IP forwarding support
- IP packet filtering
- Break over SSH support
- Port triggers with SMNP and email alerts
- Offline data logging (Syslog, NFS, CIFS)
- Online data buffering and logging
- Multiple users per port (with port sniffing)
- Telnet/SSH/Raw TCP connect
- RFC 2217 - Port Redirection
- Integrated AJAX serial console and system terminal via web interface
- Native IPMI 1.5 and 2.0 (RMCP/RMCP+) support for BMC and service processor access and control
- Service processor access (IPMI, ILO, LOM and more)
- Access to KVM built in to service processors (DRAC, RSA)
- Limit user access by LAN device and SDT service for that device
- Port triggers with SMNP and email alerts for all tunnel traffic
- Each gateway can port forward to an unlimited number of locally networked hosts (computers, routers)
- Embedded DHCP server for management LAN devices
- Network UPS Tools for UPS Monitoring and Management
- PowerMan for PDU and RPC Management
- Command Line interface (Linux Shell)
- NAGIOS distributed monitoring
- Out-of-band (dial-up modem access) included - V.92 Serial Data/Fax Embedded Modem 3.3V Model, 14.4K Fax
- Linux with source code access
- Constructed of heavy-duty steel housing
- 1U rackmount

Specifications

OVERVIEW	
Multi-User	Yes
INPUT	
Maximum Input Amps	0.8
Input Connection Type	2 x IEC-320-C14, Auto-Switching 100-240VAC



PHYSICAL	
Unit Dimensions (hwd / in.)	1.75 x 17.40 x 12.50
Unit Dimensions (hwd / cm)	4.445 x 44.2 x 31.75
Unit Weight (lbs.)	8.7
Unit Weight (kg)	3.95
Color	Black
ENVIRONMENTAL	
Storage Temperature Range	Non operating storage temperature: -30C to +60C (-20F to +140F)
Relative Humidity	Humidity: 5% to 90%
Operating Temperature	Ambient operating temperature: 5C to 50C (41F to 122F)
BTUs	120V: 68 BTU per hour
Power Consumption (Watts)	120V: 20 Watts
COMMUNICATIONS	
IP Remote Access	Yes
CONNECTIONS	
Ports	48
Other Ports - Port 1	1 x DB-9 RS-232 local console and modem serial port (2400 to 115,200 bps)
Other Ports - Port 2	1 RJ-11 modem port
Other Ports - Port 3	2 x RJ-45 10/100Base-T Ethernet port
Other Ports - Port 4	1 USB port
Other Ports - Port 5	2 x C14 Power Ports, 100-240V AC
CERTIFICATIONS	
Approvals	FCC Part 15 A, UL 1950, CE (EN55022 A, EN55024, EN60950), TUV, C-Tick
WARRANTY	
Product Warranty Period (Worldwide)	2-year limited warranty

© 2015 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice.

Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:

<http://www.triplite.com/products/product-certification-agencies>