


T-3¼ MINIATURE BAYONET BASE

MINIATURE LAMP

6.3V .250A

WAMCO PART NO.		ENVELOPE SIZE		BASE TYPE	RATING		FILAMENT SHAPE	
WL-44		T-3¼		BA9s	6.3V .250A		C-2R	
TEST VOLTS	CURRENT (A)			LIGHT OUTPUT (MSCP)			LIFE HRS	
	MIN	NOM	MAX	MIN	NOM	MAX		
	6.3V	.225	.250	.275	.675	.900		1.125
							3,000	

DIMENSIONAL CHARACTERISTICS



NOTES

1. LCL = .78" (19.8mm)
2. Nickel-plated brass construction base
3. Part mark WL-44
4. RoHS compliant
5. ANSI trade number 44
6. Military standard MS15571-1

