

Palm Size Digital Multimeter **TENMA™**



Specifications:

Basic Functions	Range	Best Accuracy
DC Voltage	200mV/2,000mV/20V/200V/600V	±(0.5%+2)
AC Voltage	200V/600V	±(1.2%+3)
DC Current	2,000µA/20mA/200mA/10A	± (1%+2)
Resistance	200Ω/2,000Ω/20kΩ/200kΩ/2,000kΩ/20MΩ/200MΩ	±(0.8%+5)

Special Functions

Display Count		2,000
Manual Range		√
Square Wave Output		√
Diode		√
Low Battery Indication		√
Data Hold		√
Input Impedance for DCV	Around :10MΩ	√

General Characteristics

Power	9V Battery (6F22)
LCD Size	49mm × 18mm
Product Colour	Orange and Grey
Product Net Weight	200g
Product Size	72mm × 137mm × 35mm
Standard Accessories	Battery, Test Lead

Part Number Table

Description	Part Number
Palm Size Digital Multimeter	72-2655

Important Notice : This data sheet and its contents (the "Information") belong to the members of the Premier Farnell group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Tenma is the registered trademark of the Group. © Premier Farnell plc 2012.