

**EVEREADY BATTERY CO.** 

Internet: www.energizer.com

## **ENERGIZER NO. 409**

1-800-383-7323 / USA 1-800-383-7323 / CANADA + 44 (0) 208 920 2306 / EUROPE

### 6V

**CLASSIC** 

Zinc-Manganese Dioxide (Zn/MnO<sub>2</sub>) **Chemical System:** 

(No Added Mercury or Cadmium)

Designation: ANSI-915, IEC-4R25

**Battery Voltage:** 6.0 Volts

**Operating Temp:** -18°C to 55°C (0°F to 130°F)

Average Weight: 600 grams (21.2 oz.)

Volume: 488 cubic centimeters (30 cubic inch)

Average Capacity: 11 Ah to 0.8 volts / cell


(Rated at 25k ohms continuous at 21°C)

Cell: Four No. 60 (size "F") in series

Jacket: Plastic

# 22.20 (0.874) Typical

**Industry Standard Dimensions in mm (inches)** 



THIS BATTERY WILL PASS FREELY THROUGH A CYLINDRICAL TUBE 82.6 DIAMETER x 101.6 LONG

#### **INTERNAL RESISTANCE VS. TEMPERATURE**


The measurement is an approximation of the battery's actual internal resistance. It is sensitive to the loads and operator technique.

Schedule: Background Load 600 ohms Pulse Load 10 ohms


Pulse Duration 1 second

| Temperature  | Typical Ri (ohms) |
|--------------|-------------------|
| 45°C (113°F) | 0.7               |
| 21°C (70°F)  | 8.0               |
| 0°C (32°F)   | 1.0               |
| -21°C (-4°F) | 10.0              |

### CONSTANT RESISTANCE PERFORMANCE



#### CONSTANT CURRENT DISCHARGE **Typical Service**



#### **Important Notice**

This data sheet contains information specific to batteries manufactured at the time of its publication. Contents herein do not constitute a warranty.

Form No. EBC - 3106D Page 1 of 2





### ENGINEERING DATASHEET

EVEREADY BATTERY CO. Internet: www.energizer.com

# **ENERGIZER NO. 409**

## **Typical Applications**







#### **Important Notice**

This data sheet contains information specific to batteries manufactured at the time of its publication.

Contents herein do not constitute a warranty.

Form No. EBC - 3106D Page 2 of 2