


AIR CURTAIN NFJ300



Features:

- Ceiling or wall mounting (vertical or horizontal)
- c/w easy fix bracket
- 3 switched controls for fan only and 2 heat settings
- 2 heat settings (1500W and 3000W)
- Pressed steel epoxy coated body

Installation:



Specifications:

Voltage:	240V~/50Hz, Class I
Rated Power:	3000W
Current:	14.5A
Air Volume:	254m ³ /hrs
Air Velocity(max):	4.8m/sec
Noise Level:	60dB
Net Weight:	5.2Kg

Packing:

Dimension:	620×155×230mm
Gross Weight:	5.9Kg

Container Loading:

20ft container:	1290pcs
40ft container:	2690pcs
40HQ container:	2959pcs