

MPG Multi-Purpose Grease

MPG is a general purpose lubricant suitable for use in a vast array of mechanical and electrical applications.

- Excellent general purpose lubricant; ideal for a vast array of applications
- Wide temperature range; good performance in environments with varying temperature conditions
- Good lubricating and thermal properties; versatile in use
- Good plastics compatibility; safe on most thermoplastics, although testing is always advised

Approvals **RoHS-2 Compliant (2011/65/EU):** **Yes**
NATO Stock Numbers: **9150-99-660-1415**

Typical Properties

Colour	Light Brown
Temperature Range (°C)	-20 to +200
Evaporation Weight Loss (% 7 days @ 125°C)	3.1
Drop Point (IP32 / ISO 2176 (°C))	>250
Cone Penetration Un-worked (ASTM D 217 @ 20°C)	275
Thickener	Clay
UV Trace	No

Electrical Properties

Dielectric Strength (kV/mm)	30
-----------------------------	----

Base Oil Properties

Base Oil Type	Mineral Oil
Base Oil Viscosity @ 40°C (Kinematic Viscosity (cSt))	463
Pour Point (ASTM D 97 (°C))	-11
Flash Point (COC ASTM D 92 (°C))	230

Mechanical Properties

4 Ball Wear (mm)	2.261
Weld Load (kgf)	160

Description

Multi-Purpose Grease

Packaging

50ml Tube

Order Code

EMPG50T

Shelf Life

48 Months

Revision 1: Jan 2014

Copyright Electrolube 2013

All information is given in good faith but without warranty. Properties are given as a guide only and should not be taken as a specification.

Electrolube cannot be held responsible for the performance of its products within any application determined by the customer, who must satisfy themselves as to the suitability of the product.

Ashby Park, Coalfield Way,
Ashby de la Zouch,
Leicestershire LE65 1JR
T +44 (0)1530 419 600
F +44 (0)1530 416 640
BS EN ISO 9001:2008
Certificate No. FM 32082