

Design

No. of contacts

Contact spacing

Contact resistance

Working current

Clearance

Creepage

Mating cycles

RoHS - compliant

Insulator material

UL file

Leadfree

Material

Color

1.11 .1

Hot plugging

Temperature range Termination technology

Insertion and withdrawal force

Insulation resistance

Test voltage

**General information** 

# **DIN** power female connector

IEC 60603-2

<u>></u> 10<sup>12</sup> Ohm

min. 1,6 mm

min. 3,0 mm

24pol. ≤ 37N

45pol. ≤ 70N

E102079

Yes

Yes

No

-55℃ ... +125℃

1550V contact/contact

< 15 mOhm for wirewrap and solder</p>

6 A@20℃ (see derating diagram)

- PL1 acc. to IEC 60 603-2 =>

- PL2 acc. to IEC 60 603-2 =>

- PL3 acc. to IEC 60 603-2 =>

solder pins, soldering eye, wirewrap, crimp

32pol. ≤ 50N

48pol. ≤ 75N

PBT (thermoplastics, glass fiber reinforcement 30%)

0.20

40

60

max. 48 5.08 mm types: F, F9 female



3,81mm between rows

2500V contact/ground

500 mating cycles

400 mating cycles

50 mating cycles


## **Soldering instructions**

The connectors should be protected when being soldered in a dip, flow or film soldering baths. Otherwise, they might become contaminated as a result of soldering operations or deformed as a result of overheating.

(1) For prototypes and short runs protect the connectors with an industrial adhesive tape, e.g. Tesaband 4331 (www.tesa.de). Cover the underside of the connector moulding and the adjacent parts of the pcb as well as the open sides of the connector. This will prevent heat and gases of the soldering apparatus from damaging the connector. About 140 + 5 mm of the tape should suffice.

(2) For large series a jig is recommended. Its protective cover with a fast action mechanical locking device shields the connectors from gas and heat generated by the soldering apparatus. As an additional protection a foil can be used for covering the parts that should not be soldered.

### Cross section of solder pins



## Installation of crimp contacts

#### Fitting the crimp contacts

After crimping the wires onto the contacts with the help of a crimping tool or an automatic crimping machine the contacts should be correctly oriented and inserted into the cavities of the connector moulding in the required configuration. They snap into position and are firmly held in place. A light pull on the wire assures the correct tensile strength of the contact. When using stranded wires with a gauge below 0.37 mm<sup>2</sup> an insertion tool is necessary.

#### Removing the crimp contacts

The removal tool is inserted into a slot on the side of the respective crimp cavity. This action compresses the contact retaining spring therefore the contact can then be easily withdrawn using a light pull on the wire. This action will cause no damage to the contact/wire which can be repositioned/refitted as necessary. The drawing demonstrates the crimp removal procedure (max. 5x).

Date

28/04/11

28/04/11

Name

nte

TD

UL classification	UL 94-V0	
Material group acc. IEC 60664-1	IIIa (175 <u>&lt;</u> CTI <	< 400)
NFF classification	I3, F4	
Contact material		
Contact material	Copper alloy	
Plating termination zone	Sn over Ni for so	solder, Ni for wirewrap and crimp
Plating contact zone	Au over Ni	crimp PL1: Au over PdNi over Ni crimp PL2: Au over Ni
The current carrying capacity is limited by maximum		
temperature of materials for inserts and contacts including terminals.	J	5
The current capacity curve is valid for continuous, nor	า	
interrupted current loaded contacts of connectors wher		
simultaneous power on all contacts is given, without exceeding the maximum temperature.	J	
Control and test procedures according to DIN IEC 60512-5		Electrical load [A]
		<sup>ш</sup>

Contact material		
Contact material	Copper alloy	
Plating termination zone	Sn over Ni for solder, Ni for wirewrap and crimp	
Plating contact zone	Au over Ni crimp PL1: Au over PdNi over Ni	
	crimp PL2: Au over Ni	

RAL 7032 (grey)

