



LP Series LED Beacon

The LP is a low profile LED mini beacon. This range of beacons is suitable for forklift trucks, material handling, machine guard and warning, machine fault indication, process line status indication and automated door indicators. The LP LED is available in 5 colours.

Models

PART NO.	VOLTAGE	AMPS (Flashing)	AMPS (Constant)	COLOUR
30000163	10-100Vdc, 10-100Vac	110mA @ 12Vdc, 55mA @ 24Vdc, 35mA @ 50Vac, 25mA @ 100Vac	80mA @ 12Vdc, 40mA @ 24Vdc, 25mA @ 50Vac, 20mA @ 100Vac	Clear
30000263	10-100Vdc, 10-100Vac	110mA @ 12Vdc, 55mA @ 24Vdc, 35mA @ 50Vac, 25mA @ 100Vac	80mA @ 12Vdc, 40mA @ 24Vdc, 25mA @ 50Vac, 20mA @ 100Vac	Amber
30000363	10-100Vdc, 10-100Vac	110mA @ 12Vdc, 55mA @ 24Vdc, 35mA @ 50Vac, 25mA @ 100Vac	80mA @ 12Vdc, 40mA @ 24Vdc, 25mA @ 50Vac, 20mA @ 100Vac	Red
30000463	10-100Vdc, 10-100Vac	110mA @ 12Vdc, 55mA @ 24Vdc, 35mA @ 50Vac, 25mA @ 100Vac	80mA @ 12Vdc, 40mA @ 24Vdc, 25mA @ 50Vac, 20mA @ 100Vac	Blue
30000563	10-100Vdc, 10-100Vac	110mA @ 12Vdc, 55mA @ 24Vdc, 35mA @ 50Vac, 25mA @ 100Vac	80mA @ 12Vdc, 40mA @ 24Vdc, 25mA @ 50Vac, 20mA @ 100Vac	Green

Features and Benefits

- 360° Visibility
- Voltage: 10-100Vdc and 10-100Vac
- Operating temperature -20°C to +60°C
- High voltage transient and polarity reversal protection fitted
- Polycarbonate base and lens
- IP67 when installed correctly
- Reduced output 'steady burn' function
- CE

