



Description

- Meets EN 61340-5-1
- 2.5mm polyurethane insulation
- Retracted Length: 0.7 m
- Extended Length: 3 meters
- Conductor is high strength 7-end duplex tinsel for strength and flexibility
- 1 megohm current limiting resistor built in each socket, power rating of 25 watt
- Dielectric Strength: Cord withstand 1250 volts DC for at least one minute
- Both ends terminated with a 10mm female snap socket
- Colour: Black

"EPA ground cords shall be used to make electrical connections between groundable points and the EPA ground facility.

Where a single resistor is used in the EPA ground cord, this shall be located near the groundable point. Where more than one resistor of a minimum resistance value of one half the total resistance shall be located near the groundable point.

When accessible, the EPA ground cord and its groundable point connection shall be shrouded by insulating material." (EN 61340-5-1 section 5.3.4 ground cords)

Per Note 6 of Table 1 of EN 61345-5-1 for Working surfaces, storage racks, trolleys and carts "It is allowed, when approved by the ESD co-ordinator, to use surfaces which are 'hard ground' i.e. less than 1×10^4 ohms to EPA ground."

Item	Description
VER-26195	Coiled Cord, 3m, 2x10mm Sockets, Black



Made in the
United Kingdom

Unless otherwise noted, tolerance is $\pm 10\%$
Special manufactured items are not returnable for credit.

Vermason

Coiled Cord, 3m, 2x10mm Sockets

VERMASON
UNIT C, 4TH DIMENSION, FOURTH AVENUE, LETCHWORTH,
HERTS, SG6 2TD UK
PHONE: +44 (0) 1462-672005, FAX: +44 (0) 1462-670440
E-MAIL: Service@Vermason.co.uk, INTERNET: Vermason.co.uk

Drawing Number
VER-26195

DATE:
December
2015