

T50LDH9C2

Article Number: 117-05402

Double Head Tie, 15.6" Long, 50lb Tensile Strength, PA66, Natural, 100/pkg



Download drawing



Download spec sheet

Base Data

Local Order Number T50LDH9C2
Type T50LDH
Color Natural (NA)

Features and Benefits

- The tie contains a dual locking design to secure two bundles at once.
- Head design can also provide spacing between parallel bundles.
- Bent tail allows for quick insertion into head.

Product Description The double head cable tie was designed with a dual locking head to secure two bundles simultaneously. The head also provides separation between bundles or bundles running parallel to each other. The bent tail design allows quick and simple installations by hand. For high volume applications, tensioning tools are available to ensure consistent and safe installation.

Short Description Double Head Tie, 15.6" Long, 50lb Tensile Strength, PA66, Natural, 100/pkg

Product Dimensions

Minimum Tensile Strength (Imperial) 50.0 lbs

Minimum Tensile Strength (Metric) 225.0 N

Length L (Imperial) 15.6 "

Length L (Metric) 395.0 mm

Bundle Diameter 2nd Loop Max. (Imperial) 2.0 "

Fixation MethodNone

Identification Plate Position none

Releasable Closure No

Tie Closure plastic pawl

Variant Inside Serrated

Width W (Imperial) 0.19 "

Width W (Metric) 4.7 mm

Bundle Diameter Min. (Imperial) 0.06 "

Bundle Diameter Min. (Metric) 1.6 mm

Bundle Diameter Max. (Imperial) 2.0 "

Bundle Diameter Max. (Metric) 50.0 mm

Bundle Diameter 1st Loop Max. (Imperial) 4.0 "

Bundle Diameter 1st Loop Max. (Metric)101.6 mm

Thickness T (Imperial) 0.055 "

Cable Tie Head Length (Imperial) 0.53 "

Cable Tie Head Width (Imperial) 0.32 "

Bundle Diameter 2nd Loop Max. 50.8 mm
(Metric)

Thickness T (Metric) 1.4 mm

Logistics and Packaging

Quantity Per bag
Package Quantity (Metric) 100
Carton Quantity 5000

Material and Specifications

Material Polyamide 6.6 (PA66)
Material Shortcut PA66
Flammability UL94 V2
Halogenfree Yes
Operating Temperature -40°F to +185°F (-40°C to +85°C)
ROHS Compliant Yes
Certification/Specification UL
UL Listed (US and Canada) No
UL Recognized (US and Canada) Yes