

Type: Male connector straight with 5 rows

Termination: Press-fit

Number of contacts: 55, 77

Pitch: 2 mm

Operational current: 1.5 A


Packaging: Tube

Standard: IEC 61076-4-101



Technical Specifications on page 204

Dimensions in mm



For detailed drawings visit www.ept.de

Accessories

- Processing tools p. 318
- Shroud p. 266

Note

- Pin lengths p. 209

Mating connector / Application:



Type C Female connector (p. 240)



Press-fit - Performance level II

No. of contacts	Contact arrangement	PCB thickness > 2.2 mm
		Part number
55		243-31010-15
55		243-31020-15
77		243-31310-15
77		243-31320-15

On request

- contact arrangement
- other contact surface

Ordering note

- PCB thickness 1.4 - 2.2 mm
(Part number 243-31xxx-05)