

Product Specification

General

Batteries, in all their aspects, should be in accordance with IEC 60086-1 and IEC 60086-2

1. Model no. **PRO-ELEC** Alkaline LR03

2. Nominal voltage 1.5Volt

Open circuit voltage 1.5Volt+0.15/-0

3. Nominal capacity 1100mAh

(Test condition:75Ω Load, continuous discharge, and end voltage 0.9V)

4. Average weight 12±0.5g

5.Shelf life 60Month

6. Performance

Battery service life should meet the values as stated in Table I

Table I

Discharges					
Test condition			Average duration ¹⁾ at 20°C		
Load	Daily period	End voltage	Initial	After 12 months storage ²⁾	After 36 months storage ²⁾
75Ω	4 h/d	0.9V	65.0 h	58.9 h	54.4h
10Ω	1 h/d	0.9V	7.5 h	7.2 h	6.6 h
20Ω	continuous	0.9V	16.5 h	14.4 h	13.3h
5.1Ω	4 min/h-8h/d	0.9V	3.5h	3.2h	3.0h

3.6Ω	15 sec/min	0.9V	560 pulses	520 pulses	475 pulses
------	------------	------	------------	------------	------------

¹⁾ Average service life will be calculated without the highest and the lowest of 9 samples

²⁾ Storage conditions: temperature 20±2°C and the Relative Humidity shall be 65±20%

7. Heavy metal content: Mercury(Hg) content should be less than 1 PPM

Cadmium (Cd) content should be less than 5 PPM

Lead (Pb) content should be less than 15 PPM

8. QUALITY ASSURANCE

DESCRIPTION	AQL
Battery dimensions	0.65%
Appearance	1.00%
Off load voltage	0.65%
On load voltage	1.00%
Service Output	Note 1
Leakage 6.1	0.65% (Note 2)
6.2	Note 3
6.3	Note 4

Note 1 : Acceptance/rejection in accordance with IEC publication
(1993) 86-1

Sub-clause 8.8.

Note 2 : Leakage on arrival at warehouse is within two months after shipping.

Note 3 : Sample size : n = 20
Judgement : Ac = 1, Re = 2

Note 4 : Sample size : n = 20
Judgement : Ac = 0, Re = 2

9. PACKAGING

Packaging shall be a form agreed by both parties.


PRECAUTION & HANDLING

- (1) Do not disassemble or short-circuit batteries.
- (2) Do not recharge batteries.
- (3) Do not dispose of batteries in fire.
- (4) Do not allow metal objects to contact the battery terminals.
- (5) Do not mix with used or other battery type (such as alkaline with carbon zinc).
- (6) Do not solder the batteries directly. If soldering or welding connection to the battery is required, consult our engineer for proper methods.
- (7) Do not over-discharge batteries. Force discharging batteries by external power source in a series may cause explosion.
- (8) To install or remove batteries, follow the equipment manufacturer's instructions.
- (9) Keep battery away from small children. If swallowed, consult a physician at once.
- (10) Remove batteries from device when it is not in use.

STORAGE

- (1) Store in cool, dry place before use.
- (2) Do not keep batteries at temperature of 45 or above
- (3)

Drawing 1: Dimensions of Battery (Super Ring LR03)



Product Specification

General

Batteries, in all their aspects, should be in accordance with IEC 60086-1 and IEC 60086-2

1. Model no. **PRO-ELEC** Alkaline LR6

2. Nominal voltage 1.5Volt

Open circuit voltage 1.5Volt+0.15/-0

3. Nominal capacity 2600mAh

(Test condition: 43Ω Load, continuous discharge, and end voltage 0.9V)

4. Average weight 24±1g

5. Shelf life 60Month

6. Performance

Battery service life should meet the values as stated in Table I

Table I

Discharges					
Test condition			Average duration ¹⁾ at 20°C		
Load	Daily period	End voltage	Initial	After 12 months storage ²⁾	After 36 months storage ²⁾
43Ω	4 h/d	0.9V	80.0 h	73.6 h	68.0 h
10Ω	1 h/d	0.9V	18.0 h	16.6 h	15.3 h
10Ω	continuous	0.9V	18.2h	16.7h	15.5 h
3.9Ω	1 h/d	0.9V	6.5 h	6.0 h	5.5 h
1.8Ω	15 sec/min	0.9V	550 pulses	506 pulses	468pulses

1)Average service life will be calculated without the highest and the lowest of 9 samples

2)Storage conditions: temperature $20\pm 2^{\circ}\text{C}$ and the Relative Humidity shall be $65\pm 20\%$

7. Heavy metal content: Mercury(Hg) content should be less than 1PPM

Cadmium (Cd) content should be less than 5 PPM

Lead (Pb) content should be less than 15 PPM

8. QUALITY ASSURANCE

DESCRIPTION	AQL
Battery dimensions	0.65%
Appearance	1.00%
Off load voltage	0.65%
On load voltage	1.00%
Service Output	Note 1
Leakage 6.1	0.65% (Note 2)
6.2	Note 3
6.3	Note 4

Note 1 : Acceptance/rejection in accordance with IEC publication
(1993) 86-1

Sub-clause 8.8.

Note 2 : Leakage on arrival at warehouse is within two months after shipping.

Note 3 : Sample size : $n = 20$
Judgement : $Ac = 1, Re = 2$

Note 4 : Sample size : $n = 20$
Judgement : $Ac = 0, Re = 2$

9. PACKAGING

Packaging shall be a form agreed by both parties.

PRECAUTION & HANDLING

- (1) Do not disassemble or short-circuit batteries.
- (2) Do not recharge batteries.
- (3) Do not dispose of batteries in fire.
- (4) Do not allow metal objects to contact the battery terminals.
- (5) Do not mix with used or other battery type (such as alkaline with carbon zinc).
- (6) Do not solder the batteries directly. If soldering or welding connection to the battery is required, consult our engineer for proper methods.
- (7) Do not over-discharge batteries. Force discharging batteries by external power source in a series may cause explosion.
- (8) To install or remove batteries, follow the equipment manufacturer's instructions.
- (9) Keep battery away from small children. If swallowed, consult a physician at once.
- (10) Remove batteries from device when it is not in use.

STORAGE

- (1) Store in cool, dry place before use.
- (2) Do not keep batteries at temperature of 45 or above
- (3)

Drawing 1: Dimensions of Battery (LR6/AA Size)

