



## ProVue LED Magnifying Lamp 8-Diopter

The new ProVue LED 8D workbench lamp reduces eye strain and vision fatigue for high-volume industrial users. With high magnification and bright lighting, this latest magnification lamp in the ProVue line from Aven, Inc. is also well suited for repair operations and scientific research labs. It is equipped with 45 white SMD energy efficient LEDs that provide shadow free illumination and a 5" crystal clear 8 diopter (3x) glass lens to provide 360° distortion free viewing. The white metal housing is mounted to a 45" spring balanced arm that stays set in any position. Lamp operates at 115 V-AC and comes complete with mounting clamp and 5 foot power cord.

### Features

- 45 white SMD energy efficient LEDs provide shadow free illumination
- LED Life: Minimum 20,000 hours
- 5" crystal clear glass lens, 8 diopter (3x)
- 45" spring balanced arm with tension adjustment knobs; stays set in any position
- Metal Housing for Durability
- Comes with a 5ft power cord and Mounting Clamp
- 1 year warranty

| PROVUE LED MAGNIFYING LAMP 8-DIOPTER |  |
|--------------------------------------|--|
| <b>MAGNIFICATION</b>                 | 3.00X (8 Diopter)  |
| <b>LENS DIAMETER</b>                 | 5 Inches   |
| <b>ADJUSTABLE ARM LENGTH</b>         | 45 Inches  |
| <b>COLOR</b>                         | White  |
| <b>LIGHTING</b>                      | 45 white SMD LED lights  |
| <b>LED LIFE</b>                      | Minimum 20,000 hours   |
| <b>MAGNIFYING LAMP ACCESSORIES</b>   | 26501-RBLED, replacement board with 45 LEDs<br>26501-AL3, Auxiliary Lens - 3 Diopter (1.75x)<br>26501-SLA, Swing-Away Lens - 5 Diopter (2.25x) |
| <b>WEIGHT</b>                        | 6.5 lb   |

| Part #              | Description                                 | Price           |
|---------------------|---|-----------------|
| <b>26501-LED-8D</b> | <b>ProVue LED Magnifying Lamp 8-Diopter</b> | <b>\$159.95</b> |