

HIGH SENSITIVE DRILLING MACHINE TECHNO 007 MR

- Professional drilling machine for small applications.
- In line coupling for dust suction
- Large working area
- Adjustable rotation speed 10 000 to 33 000 rd/mn
- Integrated low tension light
- Flexible and precise chuck descent
- Safety guard



Electrical Supply : 230 V. - 50/60Hz

Capacity : \varnothing 0.8 to 3.2 mm

Power : 125 W

Max. drilling capacity : 120 mm

Working table : 250 x 150 mm

Spindle travel : 6 mm

Clamping chuck : Yes

Low tension light : Yes

Connection pipe for dust : Yes

External dimensions : 250 x 150 x 260 mm

Net weight : 4.3 kg

Adjustable rotation speed : 11 000 to 33 000 rpm