



The 5CX1500A is designed for use as a Class C rf power amplifier in radio frequency applications. For FM broadcast service, the 5CX1500B is recommended in place of the 5CX1500A, for improved reliability.



5CX1500A

CHARACTERISTICS

Plate Dissipation (Max.) 1,500 Watts
Screen Dissipation (Max.) 75 Watts
Grid Dissipation (Max.) 25 Watts
Frequency for Max. rating (CW) 110 MHz
Amplification Factor 5.5

Filament/Cathode Thoriated Tungsten

Voltage 5.0 Volts Current 40.0 Amps

Capacitance Grounded Cathode

 $\begin{array}{cc} \text{Input} & 75.0 \text{ pf} \\ \text{Output} & 16.5 \text{ pf} \\ \text{Feedthrough} & 0.2 \text{ pf} \end{array}$

Capacitance Grounded Grid
Input 34.5 pf
Output 16.5 pf
Feedthrough .05 pf
Cooling Forced Air

Special Ring/ Breechblock

Air Socket SK-840
Air Chimney SK-806
Boiler ---

 Length
 4.95 in; 125.70 mm

 Diameter
 3.37 in; 85.60 mm

 Weight
 30 oz; 850 gm

		MAXIMUM RATINGS		TYPICAL OPERATION				
Class of Operation	Type of Service	Plate Voltage (Volts)	Plate Current (Amps)	Plate Voltage (Volts)	Screen Voltage (Volts)	Plate Current (Amps)	Drive Power (Watts)	Output Power (kiloWatts)
С	RF amplifier	5,000	1.0	4,500	500	0.90	9.0	3.18
С	RF Amplifier plate modulated	3,500	0.8	3,200	500	0.80	10.0	1.958
AB1	RF linear amplifier	4,000	1.0	4,000	500	0.70		1.785
AB1	AF amplifier or modulated	4,000	1.0	3,800	500	1.3		3.22

Base

The values listed above represent specified limits for the product and are subject to change. The data should be used for basic information only. Formal, controlled specifications may be obtained from CPI for use in equipment design.



For information on this and other CPI products, visit our website at: www.cpii.com, or contact: CPI MPP Division, Eimac Operation, 607 Hansen Way, Palo Alto, CA 94303

TELEPHONE: 1(800) 414-8823. FAX: (650) 592-9988 | EMAIL: powergrid@cpii.com