



VS-211HA

2x1 Automatic HDMI Standby Switcher



The VS-211HA is a high-performance automatic standby switcher for HDMI video and unbalanced stereo audio signals. The VS-211HA can be used as a manual 2x1 switcher or automatic switcher. The switcher uses a priority input or last connected input.

FEATURES

- Max. Data Rate - 6.75Gbps (2.25Gbps per graphic channel).
- HDMI & HDCP Compliant.
- HDTV Compatible.
- Advanced Auto Switching - Based on video clock detection.
- Automatic Output Shutdown - If no input signal is detected after a configurable idle period.
- 3D Pass Thru.
- EDID PassThru - Passes EDID signals from display to source.
- Audio Return Channel (ARC) Pass Through.
- Parallel Unbalanced Stereo Audio Switching.
- Contact Closure Remote Control - For manual switching override.
- DIP-Switches - For setting the switching mode.

TECHNICAL SPECIFICATIONS

INPUTS:	2 HDMI connectors, 2 unbalanced stereo audio on 3.5mm mini jacks.
OUTPUTS:	1 HDMI connector, 1 unbalanced stereo audio on a 3.5mm mini jack.
MAX. DATA RATE:	6.75Gbps (2.25Gbps per graphic channel).
COMPLIANCE WITH HDMI STANDARD:	Supports HDMI and HDCP.
CONTROLS:	Contact closure on a 3-pin terminal block, 2 priority DIP-switches.
INDICATORS:	ON and active input LEDs.
POWER CONSUMPTION:	5V DC, 120mA (without load), 350mA (fully loaded).
OPERATING TEMPERATURE:	0° to +40°C (32° to 104°F).
STORAGE TEMPERATURE:	-40° to +70°C (-40° to 158°F).
HUMIDITY:	10% to 90%, RHL non-condensing.
DIMENSIONS:	12cm x 7.2cm x 2.4cm (4.7" x 2.8" x 0.9") W. D. H.
WEIGHT:	0.3kg (0.66lbs).
INCLUDED ACCESSORIES:	Power supply.
OPTIONS:	RK-3T 19" rack adapter.

