

# Single phase, primary switched mode power supply **PEL 230/12-6,5**



## Advantages

Stabilised and adjustable output voltage
DC OK signalling via LEDs
Parallel connection option
Service-friendly spring-loaded connector system
Panel installation on mounting rails

## Applications

Primary switch mode power supply is concentrated on the core task of voltage and current supply. Flat step profile optimized for installation in control panels in the building automation.

## Standards

Primary switched mode power supply  
to UL 60950, UL 508

Safety:  
EN 61558-2-16, EN 60950-1

EMC:  
EN 61204-3

## Approvals




UL/CSA 60950 recognised, UL508 listed, Germanischer Lloyd



# Single phase, primary switched mode power supply PEL 230/12-6,5

Type	PEL 230/12-6,5
<b>Electrical data</b>	
<b>Input</b>	
Input rated voltage	100 - 240 Vac
Input voltage range	85 - 264 Vac (120 - 373 Vdc)
Input rated current (rated load)	1.5 / 0.5 A (110 / 230 Vac)
Rated frequency range	44 - 66 Hz / 0 Hz
Starting current limiter	<30 A, NTC
Input fuse internal	4 A
Recommended back-up fuse (circuit breaker)	6 A, 10 A, 16 A, characteristics B, C
Mains buffering	15 / 100 ms
Transient surge voltage protection	Varistor
<b>Output</b>	
Output rated voltage	12 Vdc $\pm$ 2 %
Output voltage range	10.5 - 15.5 Vdc
Output rated current	6.50 A
Resistance to reverse feed max.	25 Vdc
Overload behaviour	Constant current
Ripple factor	typ. 100 mVss
Parallel connection	Yes
Serial operation	Yes
Efficiency	typ. 87 %
<b>Signaling</b>	
Power Good (DC OK)	LED green
<b>Standards</b>	
Classification	Primary switched mode power supply
<b>Approvals</b>	
Approvals	cURus, cULus, GL
<b>Environment</b>	
Ambient temperature	-25° C to +55° C
Storage temperature	-25° C to +85° C
Derating	-3 %/K > +45° C
Current capacity by any mounting position	max. 3.9 A
<b>Safety and protection</b>	
Protection index	IP 20
Safety class	II, (in closed cabinet)
<b>Order numbers</b>	
Order Number	PEL 230/12-6,5

Type	PEL 230/12-6,5
<b>Mechanical data</b>	
<b>Terminal and mounting</b>	
Connections output, (spring clamp terminal)	max. 2.5 mm <sup>2</sup>
Connections input, (spring clamp terminal)	max. 2.5 mm <sup>2</sup>
Mounting position	vertical
Fixing method	DIN Rail system TH 35
<b>Measures and weights</b>	
Weight	0.30 kg



Subjects to change.