## Single phase, primary switched mode power supply **PEL 230/24-4**



#### Standards

Primary switched mode power supply to UL 60950, UL 508

Safety: EN 61558-2-16, EN 60950-1

EMC: EN 61204-3

#### Advantages

- Stabilised and adjustable output voltage
- DC OK signalling via LEDs Parallel connection option
- Service-friendly spring-loaded connector system
- Panel installation on mounting rails

### Applications

Primary switch mode power supply is concentrated on the core task of voltage and current supply. Flat step profile optimized for installation in control panels in the building automation.





UL/CSA 60950 recognised, UL508 listed, Germanischer Lloyd





# Single phase, primary switched mode power supply **PEL 230/24-4**

	<b>T</b>			т.	
	Туре	PEL 230/24-4		Туре	PEL 230/24-4
ያደ	Input			Terminal and mounting	
٦۲ ۱+	Input rated voltage	100 - 240 Vac	30	Connections output, (spring clamp terminal)	max. 2.5 mm <sup>2</sup>
	Input voltage range	85 - 264 Vac (120 - 373 Vdc)		Connections input, (spring clamp terminal)	max. 2.5 mm <sup>2</sup>
Electrical data	Input rated current (rated load)	1.6 / 0.9 A (110 / 230 Vac)	ta	Mounting position	vertical
	Rated frequency range	44 - 66 Hz / 0 Hz	qa	Fixing method	DIN Rail system TH 35
	Starting current limiter	<30 A, NTC	<u>–</u>	Measures and weights	
	Input fuse internal	2 A (slow-blow)	<u>ö</u> .	Weight	0.30 kg
	Recommended back-up fuse (circuit breaker)	6 A, 10 A, 16 A, characteristics B, C	an		
	Mains buffering	15 / 100 ms	Mechanical data	<b>^</b>	
	Transient surge voltage protection	Varistor			
	Output				
	Output rated voltage	24 Vdc ±2 %			54.0 59.0
	Output voltage range	22,8 - 26,4 Vdc			
	Output rated current	4.00 A			
	Resistance to reverse feed max.	30 Vdc			
	Overload behaviour	Constant current			
	Ripple factor	typ. 100 mVss			
	Parallel connection	Yes			
	Serial operation	Yes			
	Efficiency	typ. 88 %			
	Signaling				
	Power Good (DC OK)	LED green			
	Standards				
	Classification	Primary switched mode power supply			
	Approvals				
	Approvals	cURus, cULus, GL			
	Environment				
	Ambient temperature	-25° C to +55° C			
	Storage temperature	-25° C to +85° C			
	Derating	-3 %/K > +45° C			
	Current capacity by any mounting position	max. 2.4 A			
	Safety and protection				
	Protection index	IP 20			
	Safety class	ll, (in closed cabinet)			
	Order numbers				

Order Number

PEL 230/24-4

