



## Safety Data Sheet

Copyright, 2014, 3M Company.

All rights reserved. Copying and/or downloading of this information for the purpose of properly utilizing 3M products is allowed provided that: (1) the information is copied in full with no changes unless prior written agreement is obtained from 3M, and (2) neither the copy nor the original is resold or otherwise distributed with the intention of earning a profit thereon.

<b>Document Group:</b>	27-7744-9	<b>Version Number:</b>	2.01
<b>Issue Date:</b>	05/29/14	<b>Supersedes Date:</b>	05/12/11

### SECTION 1: Identification

#### 1.1. Product identifier

3M™ ScotchBrite™ Ultra Fine Scuff Sponge 7442

#### Product Identification Numbers

61-5001-1414-7

#### 1.2. Recommended use and restrictions on use

##### Recommended use

Abrasive Product

#### 1.3. Supplier's details

<b>MANUFACTURER:</b>	3M
<b>DIVISION:</b>	Abrasive Systems Division
<b>ADDRESS:</b>	3M Center, St. Paul, MN 55144-1000, USA
<b>Telephone:</b>	1-888-3M HELPS (1-888-364-3577)

#### 1.4. Emergency telephone number

1-800-364-3577 or (651) 737-6501 (24 hours)

### SECTION 2: Hazard identification

#### 2.1. Hazard classification

Not classified as hazardous according to OSHA Hazard Communication Standard, 29 CFR 1910.1200.

#### 2.2. Label elements

##### Signal word

Not applicable.

##### Symbols

Not applicable.

##### Pictograms

Not applicable.

#### 2.3. Hazards not otherwise classified

None.

85% of the mixture consists of ingredients of unknown acute oral toxicity.

### SECTION 3: Composition/information on ingredients

Ingredient	C.A.S. No.	% by Wt
Silicon Carbide Mineral	409-21-2	5 - 15
Nylon Fiber	Mixture	5 - 15
Cured Resin	Mixture	15 - 40
Additive	7791-18-6	1 - 5
Water	7732-18-5	15 - 50
Cellulose	Mixture	10 - 50

### SECTION 4: First aid measures

#### 4.1. Description of first aid measures

##### Inhalation:

Remove person to fresh air. If you feel unwell, get medical attention.

##### Skin Contact:

Wash with soap and water. If signs/symptoms develop, get medical attention.

##### Eye Contact:

Flush with large amounts of water. Remove contact lenses if easy to do. Continue rinsing. If signs/symptoms persist, get medical attention.

##### If Swallowed:

No need for first aid is anticipated.

#### 4.2. Most important symptoms and effects, both acute and delayed

See Section 11.1. Information on toxicological effects.

#### 4.3. Indication of any immediate medical attention and special treatment required

Not applicable

### SECTION 5: Fire-fighting measures

#### 5.1. Suitable extinguishing media

In case of fire: Use a fire fighting agent suitable for ordinary combustible material such as water or foam to extinguish.

#### 5.2. Special hazards arising from the substance or mixture

None inherent in this product.

#### Hazardous Decomposition or By-Products

##### Substance

Carbon monoxide

Carbon dioxide

##### Condition

During Combustion

During Combustion

#### 5.3. Special protective actions for fire-fighters

No unusual fire or explosion hazards are anticipated.

## SECTION 6: Accidental release measures

### 6.1. Personal precautions, protective equipment and emergency procedures

Observe precautions from other sections.

### 6.2. Environmental precautions

Avoid release to the environment.

### 6.3. Methods and material for containment and cleaning up

Not applicable.

## SECTION 7: Handling and storage

### 7.1. Precautions for safe handling

Avoid breathing of dust created by sanding, grinding or machining. Avoid release to the environment. Combustible dust may form by action of this product on another material (substrate). Dust generated from the substrate during use of this product may be explosive if in sufficient concentration with an ignition source. Dust deposits should not be allowed to accumulate on surfaces because of the potential for secondary explosions.

### 7.2. Conditions for safe storage including any incompatibilities

No special storage requirements.

## SECTION 8: Exposure controls/personal protection

### 8.1. Control parameters

#### Occupational exposure limits

Ingredient	C.A.S. No.	Agency	Limit type	Additional Comments
Silicon Carbide Mineral	409-21-2	ACGIH	TWA(as fiber):0.1 fiber/cc;TWA(inhalable fraction):10 mg/m <sup>3</sup> ;TWA(respirable fraction):3 mg/m <sup>3</sup>	
Silicon Carbide Mineral	409-21-2	OSHA	TWA(as total dust):15 mg/m <sup>3</sup> ;TWA(respirable fraction):5 mg/m <sup>3</sup>	

ACGIH : American Conference of Governmental Industrial Hygienists

AIHA : American Industrial Hygiene Association

CMRG : Chemical Manufacturer's Recommended Guidelines

OSHA : United States Department of Labor - Occupational Safety and Health Administration

TWA: Time-Weighted-Average

STEL: Short Term Exposure Limit

CEIL: Ceiling

### 8.2. Exposure controls

#### 8.2.1. Engineering controls

Provide appropriate local exhaust ventilation for sanding, grinding or machining. Use general dilution ventilation and/or local exhaust ventilation to control airborne exposures to below relevant Exposure Limits and/or control dust/fume/gas/mist/vapors/spray. If ventilation is not adequate, use respiratory protection equipment. Provide local exhaust at process emission sources to control exposure near the source and to prevent the escape of dust into the work area. Ensure that dust-handling systems (such as exhaust ducts, dust collectors, vessels, and processing equipment) are designed in a manner to prevent the escape of dust into the work area (i.e., there is no leakage from the equipment).

#### 8.2.2. Personal protective equipment (PPE)

**Eye/face protection**

To minimize the risk of injury to face and eyes, always wear eye and face protection when working at sanding or grinding operations or when near such operations. Select and use eye/face protection to prevent contact based on the results of an exposure assessment. The following eye/face protection(s) are recommended:

Safety Glasses with side shields

**Skin/hand protection**

Wear appropriate gloves to minimize risk of injury to skin from contact with dust or physical abrasion from grinding or sanding.

**Respiratory protection**

Assess exposure concentrations of all materials involved in the work process. Consider material being abraded when determining the appropriate respiratory protection. Select and use appropriate respirators to prevent inhalation overexposure. An exposure assessment may be needed to decide if a respirator is required. If a respirator is needed, use respirators as part of a full respiratory protection program. Based on the results of the exposure assessment, select from the following respirator type(s) to reduce inhalation exposure:

Half facepiece or full facepiece air-purifying respirator suitable for particulates

For questions about suitability for a specific application, consult with your respirator manufacturer.

## SECTION 9: Physical and chemical properties

**9.1. Information on basic physical and chemical properties**

<b>General Physical Form:</b>	Solid
<b>Odor, Color, Grade:</b>	Nonwoven Abrasive Product
<b>Odor threshold</b>	<i>Not Applicable</i>
<b>pH</b>	<i>Not Applicable</i>
<b>Melting point</b>	<i>Not Applicable</i>
<b>Boiling Point</b>	<i>Not Applicable</i>
<b>Flash Point</b>	<i>Not Applicable</i>
<b>Evaporation rate</b>	<i>Not Applicable</i>
<b>Flammability (solid, gas)</b>	Not Classified
<b>Flammable Limits(LEL)</b>	<i>Not Applicable</i>
<b>Flammable Limits(UEL)</b>	<i>Not Applicable</i>
<b>Vapor Pressure</b>	<i>Not Applicable</i>
<b>Vapor Density</b>	<i>Not Applicable</i>
<b>Specific Gravity</b>	<i>Not Applicable</i>
<b>Solubility in Water</b>	Nil
<b>Solubility- non-water</b>	<i>Not Applicable</i>
<b>Partition coefficient: n-octanol/ water</b>	<i>Not Applicable</i>
<b>Autoignition temperature</b>	<i>Not Applicable</i>
<b>Decomposition temperature</b>	<i>Not Applicable</i>
<b>Viscosity</b>	<i>Not Applicable</i>

## SECTION 10: Stability and reactivity

### 10.1. Reactivity

This material is considered to be non reactive under normal use conditions.

### 10.2. Chemical stability

Stable.

### 10.3. Possibility of hazardous reactions

Hazardous polymerization will not occur.

### 10.4. Conditions to avoid

None known.

### 10.5. Incompatible materials

None known.

### 10.6. Hazardous decomposition products

<u>Substance</u>	<u>Condition</u>
None known.	

Refer to section 5.2 for hazardous decomposition products during combustion.

## SECTION 11: Toxicological information

The information below may not be consistent with the material classification in Section 2 if specific ingredient classifications are mandated by a competent authority. In addition, toxicological data on ingredients may not be reflected in the material classification and/or the signs and symptoms of exposure, because an ingredient may be present below the threshold for labeling, an ingredient may not be available for exposure, or the data may not be relevant to the material as a whole.

### 11.1. Information on Toxicological effects

#### Signs and Symptoms of Exposure

Based on test data and/or information on the components, this material may produce the following health effects:

#### Inhalation:

Dust from grinding, sanding or machining may cause irritation of the respiratory system. Signs/symptoms may include cough, sneezing, nasal discharge, headache, hoarseness, and nose and throat pain.

#### Skin Contact:

Mechanical Skin irritation: Signs/symptoms may include abrasion, redness, pain, and itching.

#### Eye Contact:

Mechanical eye irritation: Signs/symptoms may include pain, redness, tearing and corneal abrasion.

Dust created by grinding, sanding, or machining may cause eye irritation. Signs/symptoms may include redness, swelling, pain, tearing, and blurred or hazy vision.

#### Ingestion:

No health effects are expected.

#### Additional Information:

This document covers only the 3M product. For complete assessment, when determining the degree of hazard, the material being abraded must also be considered.

#### Toxicological Data

If a component is disclosed in section 3 but does not appear in a table below, either no data are available for that endpoint or the data are not sufficient for classification.

#### Acute Toxicity

Name	Route	Species	Value
Overall product	Ingestion		No data available; calculated ATE > 5,000 mg/kg
Silicon Carbide Mineral	Dermal	Rat	LD50 > 2,000 mg/kg
Silicon Carbide Mineral	Ingestion	Rat	LD50 > 2,000 mg/kg
Additive	Ingestion	Rat	LD50 2,800 mg/kg

ATE = acute toxicity estimate

#### Skin Corrosion/Irritation

Name	Species	Value
Additive		Minimal irritation

#### Serious Eye Damage/Irritation

Name	Species	Value
Additive	Rabbit	Mild irritant

#### Skin Sensitization

Name	Species	Value

#### Respiratory Sensitization

Name	Species	Value

#### Germ Cell Mutagenicity

Name	Route	Value

#### Carcinogenicity

Name	Route	Species	Value
Additive	Ingestion	Mouse	Not carcinogenic

#### Reproductive Toxicity

#### Reproductive and/or Developmental Effects

Name	Route	Value	Species	Test Result	Exposure Duration
Additive	Ingestion	Not toxic to development	Rat	NOAEL 800 mg/kg/day	during organogenesis

#### Target Organ(s)

#### Specific Target Organ Toxicity - single exposure

Name	Route	Target Organ(s)	Value	Species	Test Result	Exposure Duration

#### Specific Target Organ Toxicity - repeated exposure

Name	Route	Target Organ(s)	Value	Species	Test Result	Exposure Duration
Silicon Carbide Mineral	Inhalation	pneumoconiosis	Some positive data exist, but the data are not sufficient for classification		HHA	
Additive	Ingestion	kidney and/or bladder	Some positive data exist, but the data are not sufficient for classification	Mouse	NOAEL 11,400 mg/kg/day	13 weeks

**Aspiration Hazard**

Name	Value

Please contact the address or phone number listed on the first page of the SDS for additional toxicological information on this material and/or its components.

**SECTION 12: Ecological information****Ecotoxicological information**

Please contact the address or phone number listed on the first page of the SDS for additional ecotoxicological information on this material and/or its components.

**Chemical fate information**

Please contact the address or phone number listed on the first page of the SDS for additional chemical fate information on this material and/or its components.

**SECTION 13: Disposal considerations****13.1. Disposal methods**

Dispose of contents/ container in accordance with the local/regional/national/international regulations.

The substrate that was abraded must be considered as a factor in the disposal method for this product. Incinerate in a permitted waste incineration facility. Proper destruction may require the use of additional fuel during incineration processes. As a disposal alternative, utilize an acceptable permitted waste disposal facility.

**EPA Hazardous Waste Number (RCRA):** Not regulated

**SECTION 14: Transport Information**

For Transport Information, please visit <http://3M.com/Transportinfo> or call 1-800-364-3577 or 651-737-6501.

**SECTION 15: Regulatory information****15.1. US Federal Regulations**

Contact 3M for more information.

**311/312 Hazard Categories:**

Fire Hazard - No    Pressure Hazard - No    Reactivity Hazard - No    Immediate Hazard - No    Delayed Hazard - No

**15.2. State Regulations**

Contact 3M for more information.

### 15.3. Chemical Inventories

This product is an article as defined by TSCA regulations, and is exempt from TSCA Inventory listing requirements.

Contact 3M for more information.

### 15.4. International Regulations

Contact 3M for more information.

**This SDS has been prepared to meet the U.S. OSHA Hazard Communication Standard, 29 CFR 1910.1200.**

## SECTION 16: Other information

### NFPA Hazard Classification

**Health:** 0 **Flammability:** 1 **Instability:** 0 **Special Hazards:** None

National Fire Protection Association (NFPA) hazard ratings are designed for use by emergency response personnel to address the hazards that are presented by short-term, acute exposure to a material under conditions of fire, spill, or similar emergencies. Hazard ratings are primarily based on the inherent physical and toxic properties of the material but also include the toxic properties of combustion or decomposition products that are known to be generated in significant quantities.

**Document Group:** 27-7744-9

**Issue Date:** 05/29/14

**Version Number:** 2.01

**Supersedes Date:** 05/12/11

**DISCLAIMER:** The information in this Safety Data Sheet (SDS) is believed to be correct as of the date issued. 3M MAKES NO WARRANTIES, EXPRESSED OR IMPLIED, INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE OR COURSE OF PERFORMANCE OR USAGE OF TRADE. User is responsible for determining whether the 3M product is fit for a particular purpose and suitable for user's method of use or application. Given the variety of factors that can affect the use and application of a 3M product, some of which are uniquely within the user's knowledge and control, it is essential that the user evaluate the 3M product to determine whether it is fit for a particular purpose and suitable for user's method of use or application.

3M provides information in electronic form as a service to its customers. Due to the remote possibility that electronic transfer may have resulted in errors, omissions or alterations in this information, 3M makes no representations as to its completeness or accuracy. In addition, information obtained from a database may not be as current as the information in the SDS available directly from 3M

**3M USA SDSs are available at [www.3M.com](http://www.3M.com)**