

# R95-101




## 8-Pin Octal Socket

### Features

- Panel/Surface Mount
- Pressure Clamp Screws
- Screws: 6-32 x 5/16", Steel, Nickel Plated.

### Electrical Rating:

300 Volts, 15 Amps



# R95-102

## 10-Pin Blade Socket

### Features

- PC Board Mount

### Electrical Rating:

1000 Volts, 5 Amps

