





## High Voltage (up to 0.5 kV) Thick Film Chip Resistors



#### **FEATURES**

• High operating voltage (up to 500 V)





• Metal glaze on high quality ceramic

 Material categorization: for definitions of compliance please see <a href="https://www.vishav.com/doc?99912">www.vishav.com/doc?99912</a>

STANDARD ELECTRICAL SPECIFICATIONS								
MODEL	CASE SIZE INCH	CASE SIZE METRIC	POWER RATING P <sub>70</sub> W	LIMITINGELEMENT VOLTAGE U <sub>MAX.</sub> AC <sub>RMS</sub> /DC V	TEMPERATURE COEFFICIENT ± ppm/K	TOLERANCE ± %	$\begin{array}{c} \text{RESISTANCE} \\ \text{RANGE} \\ \Omega \end{array}$	SERIES
DCV0905 02	RCV0805 e3 0805 RR 2012M	DD 0010M	0.125	400	100	1	100K to 10M	E24; E96
HCV0003 e3		0.123	400	200	5	1001 10 10101	E24	
RCV1206 e3	1206	RR 3216M	0.25	500	100	1	100K to 10M	E24; E96
NOV 1206 63	NGV 1200 83 1206		0.25	500	200	5	TOOK TO TOWN	E24


#### **Notes**

- These resistors do not feature a lifetime limitation when operated within the limits of rated dissipation, permissible operating voltage and
  permissible film temperature. However, the resistance typically increases due to the resistor's film temperature over operating time, generally
  known as drift. The drift may exceed the stability requirements of an individual application circuit and thereby limits the functional lifetime.
- No marking.
- Power rating depends on the max. temperature at the solder point, the component placement density and the substrate material.

TECHNICAL SPECIFICATIONS					
PARAMETER	UNIT	RCV0805	RCV1206		
Rated dissipation $P_{70}$ <sup>(1)</sup>	W	0.125	0.25		
Limiting element voltage U <sub>max.</sub> AC <sub>RMS</sub> /DC	V	400	500		
Insulation voltage U <sub>ins.</sub> (1 min)	V	> 50	00		
Voltage coefficient of resistance chart	ppm/V	25	5		
Insulation resistance	Ω	> 10	09		
Operating temperature range	°C	- 55 to	+ 155		
Weight	mg	5.5	10		

#### Note


<sup>(1)</sup> The power dissipation on the resistors generates a temperature rise against the local ambient, depending on the heat flow support of the printed-circuit board (thermal resistance). The rated dissipation applies only if the permitted film temperature of 155 °C is not exceeded.






# Vishay Draloric

PACKAGING							
MODEL	CODE	QUANTITY	CARRIER TAPE	WIDTH	PITCH	REEL DIAMETER	
	EA = ET1	5000		8 mm	4 mm	180 mm/7"	
RCV0805	EB = ET5	10 000	Paper tape acc. to IEC 60068-3 Type I			285 mm/11.25"	
	EC = ET6	20 000				330 mm/13"	
	EA = ET1	5000				180 mm/7"	
RCV1206	EB = ET5	10 000	7.			285 mm/11.25"	
	EC = ET6	20 000				330 mm/13"	



### **FUNCTIONAL PERFORMANCE**





# Vishay Draloric

TEST PR	OCEDURES A	AND REQUIREME	NTS			
EN 60115-1	IEC 60068-2		PROCEDURE	REQUIREMENTS PERMISSIBLE CHANGE ( $\Delta R$ )  100 kΩ to 10 MΩ		
CLAUSE	TEST METHOD	TEST	Stability for product types:			
			RCV e3			
4.5	-	Resistance	-	± 1 %	± 5 %	
4.13	-	Short time overload	$U = 2.5 \times \sqrt{P_{70} \times R}$ $\leq 2 \times U_{\text{max.}};$ 5  s	± (0.25 % R + 0.05 Ω)	± (0.5 % R + 0.05 Ω)	
4.17.2	58 (Td)	Solderability	Solder bath method; Sn60Pb40 non-activated flux; (235 ± 5) °C (2 ± 0.2) s	Good (≥ 95 % o no visible		
4.17.2	38 (Tu)	Soluerability	Solder bath method; Sn96.5Ag3Cu0.5 non-activated flux; (245 ± 5) °C (3 ± 0.3) s	Good (≥ 95 % o no visible		
4.8.4.2	-	Temperature coefficient	(20/- 55/20) °C and (20/155/20) °C	± 100 ppm/K	± 200 ppm/K	
4.32	21 (Uu <sub>3</sub> )	Shear (adhesion)	205 N	No visible damage		
4.33	21 (Uu <sub>1</sub> )	Substrate bending	Depth 2 mm; 3 times	No visible damage, no open circuit in bent pos $\pm (0.25~\%~R + 0.05~\Omega)$		
4.19	14 (Na)	Rapid change of temperature	30 min. at - 55 °C; 30 min. at 125 °C 5 cycles	± (0.25 % R + 0.05 Ω)	± (0.5 % R + 0.05 Ω)	
		tomporataro	1000 cycles	$\pm (1 \% R + 0.05 \Omega)$	$\pm (1 \% R + 0.05 \Omega)$	
4.23	-	Climatic sequence:	-	1 (1 7071 1 0.00 11)	2 (1 70 71 1 0.00 11)	
4.23.2	2 (Ba)	Dry heat	125 °C; 16 h			
4.23.3	30 (Db)	Damp heat, cyclic	55 °C; ≥ 90 % RH 24 h; 1 cycle			
4.23.4	1 (Aa)	Cold	- 55 °C; 2 h	± (1 % R + 0.05 Ω)	± (2 % R + 0.1 Ω)	
4.23.5	13 (M)	Low air pressure	1 kPa; (25 ± 10) °C; 1 h			
4.23.6	30 (Db)	Damp heat, cyclic	55 °C; . 90 % RH 24 h; 5 cycle			
4.23.7	-	DC load	$U = \sqrt{P_{70} \times R}$			
4.25.1	-	Endurance at 70 °C	$U = \sqrt{P_{70} \times R} \le U_{\text{max.}};$ 1.5 h on; 0.5 h off;			
			70 °C; 1000 h	± (1 % R + 0.05 Ω)	± (2 % R + 0.1 Ω)	
			70 °C; 8000 h	± (2 % R + 0.1 Ω)	± (4 % R + 0.1 Ω)	
4.18.2	58 (Td)	Resistance to soldering heat	Solder bath method (260 ± 5) °C; (10 ± 1) s	± (0.25 % R + 0.05 Ω)	± (0.5 % R + 0.05 Ω)	
4.24	78 (Cab)	Damp heat, steady state	(40 ± 2) °C; (93 ± 3) % RH; 56 days	± (1 % R + 0.05 Ω)	± (2 % R + 0.05 Ω)	
4.25.3	-	Endurance at upper category temperature	155 °C; 1000 h	± (1 % R + 0.05 Ω)	± (2 % R + 0.05 Ω)	



www.vishay.com

# Vishay Draloric

TEST PROCEDURES AND REQUIREMENTS						
EN 60115-1	IEC 60068-2		PROCEDURE	REQUIREMENTS PERMISSIBLE CHANGE ( $\Delta R$ ) 100 k $\Omega$ to 10 M $\Omega$		
CLAUSE	TEST METHOD	TEST	Stability for product types:			
			RCV e3			
4.40	-	Electrostatic discharge (human body model)	IEC 61340-3-1; 3 pos. + 3 neg. discharges; ESD voltage acc. to style	± (1 % R + 0.05 Ω)		
4.29	45 (XA)	Component solvent resistance	Isopropyl alcohol; 50 °C; method 2	No visible damage		
4.30	45 (XA)	Solvent resistance of marking	Isopropyl alcohol; 50 °C; method 1, toothbrush	Marking legible, no visible damage		
4.22	6 (Fc)	Vibration, endurance by sweeping	f = 10 Hz to 2000 Hz; x, y, z ≤ 1.5 mm; A ≤ 200 m/s²; 10 sweeps per axis	± (0.25 % R + 0.05 Ω)	± (0.5 % R + 0.05 Ω)	
4.37	-	Periodic electric overload	$U = \sqrt{15 \times P_{70} \times R}$ $\leq 2 \times U_{\text{max.}};$ 0.1 s on; 2.5 s off; 1000 cycles	± (1 % R + 0.05 Ω)		
4.27	-	Single pulse high voltage overload, 10 µs/700 µs	$\hat{U} = 10 \times \sqrt{P_{70} \times R}$ $\leq 2 \times U_{\text{max.;}}$ 10 pulses	± (1 % R + 0.05 Ω)		

All tests are carried out in accordance with the following specifications:

- EN 60115-1, generic specification
- EN 140400, sectional specification
- EN 140401-802, detail specification
- IEC 60068-2-x, environmental test procedures



### **Legal Disclaimer Notice**

Vishay

### **Disclaimer**

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and/or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.

### **Material Category Policy**

Vishay Intertechnology, Inc. hereby certifies that all its products that are identified as RoHS-Compliant fulfill the definitions and restrictions defined under Directive 2011/65/EU of The European Parliament and of the Council of June 8, 2011 on the restriction of the use of certain hazardous substances in electrical and electronic equipment (EEE) - recast, unless otherwise specified as non-compliant.

Please note that some Vishay documentation may still make reference to RoHS Directive 2002/95/EC. We confirm that all the products identified as being compliant to Directive 2002/95/EC conform to Directive 2011/65/EU.

Vishay Intertechnology, Inc. hereby certifies that all its products that are identified as Halogen-Free follow Halogen-Free requirements as per JEDEC JS709A standards. Please note that some Vishay documentation may still make reference to the IEC 61249-2-21 definition. We confirm that all the products identified as being compliant to IEC 61249-2-21 conform to JEDEC JS709A standards.

Revision: 02-Oct-12 Document Number: 91000