

Technical Data Sheet

RG6/U Type SDI Coaxial Cable



2833 West Chestnut Street
 Washington, PA 15301
 Toll Free: (800) 245-4964
 Fax: (724) 222-6420
 www.westpenn-wpw.com

PART NUMBER:	6350
DESCRIPTION:	RG6/U – 1 Coaxial 18 AWG Solid- 100% Aluminum Foil + 95% Tinned Copper Braid PVC Jacket
NEC RATING:	CMR
APPROVALS:	(UL) C(UL) Listed or c(ETL)us Listed
APPLICATION:	Indoor for: SDI, Precision Video, CCTV, CATV, Digital Audio

Individual Construction Parameters:

Conductor	18 AWG Bare Copper
Stranding	Solid
Insulation Material	Gas Injected Polyethylene
Insulation Thickness	.180" Nom.
Shield	100% Al. Foil + 95% Tinned Copper Braid
Jacket Material	PVC
Overall Cable Diameter	0.275" Nom.
Bulk Cable Weight	40lbs/1000ft
Max. Recommended Pulling Tension	69lbs
Min. Bend Radius	2.75in
Flame Rating	UL 1666

Electrical & Environmental Properties:

		<u>Mhz</u>	<u>db/100ft</u>
Temperature Rating	-20deg C to 60deg C	1	.23
Max.Capacitance Between Conductors @ 1 KHz	16.2 pf/ft Nom.	10	.70
Velocity of Propagation	82% Nom.	71.5	1.67
Impedance	75 ohms Nom.	135	2.23
DC Resistance per Conductor @ 20deg C	6.5 Ohms/1M' Nom.	360	3.22
Individual Jacket Color	Black- Optional	720	5.65
RoHS Compliant	Min. Qty. other Colors	1000	6.52
SRL:	5-1600 Mhz	Yes	1000
		-23dB	2250
	1.6Ghz-4.5Ghz	-21dB	3000
		4500	14.30

Connectors and Accessories

75 ohm BNC Crimp	CN-BM73-5	Crimp Tool: TL-107	Strip Tool: TL-7503
Compression BNC 75 ohm	CN-CSBNC-6	Comp. Tool: TL-SNSA	Strip Tool: TL-CSST
Double Bubble Compression	CN-DB6BNCHD	Comp. Tool: TL-SNSA	Strip Tool: TL-CPLRBC
Compression RCA	CN-CSRCA-6	Comp. Tool: TL-SNSA	Strip Tool: TL-CSST

Specification Issue Date: 7/06

This document is the property of West Penn Wire.
 The information contained herein is considered
 Proprietary and not to be reproduced by any means
 Without written consent of West Penn Wire

Standard Lengths are 1000ft.
 The Jacket is sequentially footmarked.
 The information presented here is, to the best of our
 knowledge, is true and accurate. However, since
 conditions of use are beyond our control, all
 recommendations or suggestions are presented
 without guarantee or responsibility on our part. We
 disclaim all liability in connection with the use of
 information contained herein or otherwise.

