

# Technical Data Sheet- Indoor/Outdoor RG59/U Type CCTV Coaxial Cable



2833 West Chestnut Street  
Washington, PA 15301  
Toll Free: (800) 245-4964  
Fax: (724) 222-6420  
www.westpenn-wpw.com

<b>PART NUMBER:</b>	<b>AQC815</b>
<b>DESCRIPTION:</b>	RG59/U – 1 Conductor 20AWG Solid, 95% Bare copper braid waterblocking tape and an overall Sunlight Resistant PVC Jacket.
<b>NEC RATING:</b>	CM, CL2
<b>APPROVALS:</b>	(UL) C(UL) Listed or c(ETL)us Listed
<b>APPLICATION:</b>	Indoor/Outdoor for: Security Cable - CCTV

## Construction Parameters:

Conductor	20 AWG Bare Copper
Stranding	Solid
Insulation Material	Gas Injected Polyethylene
Insulation Thickness	.142" Nom.
Number of Conductors	1 Center Conductor
Shield	95% Bare Copper Braid
Waterblocking Tape	2 Ply
Jacket Material	Sunlight Resistant PVC
Overall Cable Diameter	0.242" Nom.
Approximate Cable Weight	17 Lbs/1M' Nom.
Flame Rating	UL 1685

## Electrical & Environmental Properties:

		<u>Mhz</u>	<u>db/100ft</u>
Temperature Rating	-20deg C to 60deg C	1	.5
Max.Capacitance Between Conductors @ 1 KHz	16.2 pf/ft Nom.	10	.68
Velocity of Propagation	82% Nom.	50	1.80
Impedance	75 ohms Nom.	100	3.0
DC Resistance per Conductor @ 20deg C	10.1 Ohms/1M' Nom.	400	4.71
Jacket Color	Black	700	6.40
RoHS Compliant	Yes	1000	7.80

## Mechanical Properties:

Max. Recommended Pull Tension	41 lbs.
Min. Bend Radius (Install)	2.5"

## Connectors and Accessories

75 ohm BNC Crimp	CN-BM74-32	Crimp Tool: TL-104	Strip Tool: TL-121
1 Pc. Compression BNC 75 ohm	CN-BNC59MCV	Comp. Tool: TL-SNSA	Strip Tool: TL-CSST
Compression RCA	CN-RCA59MCV	Comp. Tool: TL-SNSA	Strip Tool: TL-CSST

Specification Issue Date: 4/12

This document is the property of West Penn Wire.  
The information contained herein is considered  
Proprietary and not to be reproduced by any means  
Without written consent of West Penn Wire

Standard Lengths are 1000ft.  
The Jacket is sequentially footmarked.  
The information presented here is, to the best of our  
knowledge, is true and accurate. However, since  
conditions of use are beyond our control, all  
recommendations or suggestions are presented  
without guarantee or responsibility on our part. We  
disclaim all liability in connection with the use of  
information contained herein or otherwise.