49

NAVIGATION SWITCHES



FEATURES & BENEFITS

- ▶ 5-position navigation
- ► Very low profile SMT design
- ► Unique design


APPLICATIONS/MARKETS

- ► Consumer electronics where user interface is needed
- ► Handheld instrumentation
- ► Navigation
- ► Telecommunication

Contact Rating:	20mA @ 12 VDC	
Life Expectancy:	200,000 actuations	
Contact Resistance:	100mΩ MAX (INITIAL)	
Insulation Resistance:	100ΜΩ	
Dielectric Strength:	100 VAC	
Operating Temperature:	-20°C to 70°C	
Travel:	.25 ±.15 mm	

MATERIALS		
Cover:	Nickel	
Base:	Nylon	
Actuator:	Nylon	
Terminals:	Copper alloy, silver plated	
Moving Contact:	Stainless steel, silver plated	
Tape:	Teflon	






Example Ordering Number JS1300AQ


Specifications subject to change without notice.

1.00 [.039 in]

JS 1300



10.40 +.30 .409 + .012 in



Auctuation Position	Circuit
1	D - E
2	C - G
3 (Center)	F-J
4	A - H
5	B - K

