

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

26-48-1046

Status:

Active

Overview:


KK® Interconnect System - Molex

Description:

KK® 396 Breakaway Header, Right-Angle with Friction Lock, 4 Circuits, Tin (Sn) Plating

Documents:	
3D Model	Product Specification PS-08-50 (PDF)
Drawing (PDF)	RoHS Certificate of Compliance (PDF)

Agency Certification	
CSA	LR19980
UL	E29179
General	
Product Family	PCB Headers
Series	41672
Application	Power, Wire-to-Board
Application Tooling Part Link	11-20-0901
MolexKits	Yes
Overview	KK® Interconnect System - Molex
Product Name	KK® 396
UPC	800753586499
Physical	
Breakaway	Yes
Circuits (Loaded)	4
Circuits (maximum)	4
Color - Resin	Black
Durability (mating cycles max)	25
Flammability	94V-0
Glow-Wire Compliant	No
Lock to Mating Part	Yes
Material - Metal	Brass
Material - Plating Mating	Tin
Material - Resin	Polyester
Net Weight	1.684/g
Number of Rows	1
Orientation	Right Angle
PC Tail Length	5.38mm
PCB Locator	No
PCB Retention	None
PCB Thickness - Recommended	1.60mm
Packaging Type	Bag
Pitch - Mating Interface	3.96mm
Pitch - Termination Interface	3.96mm
Polarized to Mating Part	No
Polarized to PCB	Yes
Shrouded	No
Stackable	No
Temperature Range - Operating	See Product Specification
Termination Interface: Style	Through Hole
Electrical	
Current - Maximum per Contact	7.0A
Voltage - Maximum	250V
Solder Process Data	



EU RoHS

ELV and RoHS Compliant

REACH SVHC

Contains SVHC: No

Low-Halogen Status

Not Low-Halogen

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com

For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

41672Series

Mates With

2139 KK® Crimp Housing, 41695 KK® Crimp Housing, 6442 KK® Crimp Housing, 2145 PCB Connector, 41815 PCB Connector, 3069 KK® Crimp Housing

Duration at Max. Process Temperature (seconds)	5
Lead-free Process Capability	Wave Capable (TH only)
Max. Cycles at Max. Process Temperature	1
Process Temperature max. C	235
Material Info	
Old Part Number	A-41672-A04A197
Reference - Drawing Numbers	
Product Specification	PS-08-50
Sales Drawing	SD-41672-001

This document was generated on 04/23/2015

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION