

PRODUCT SPECIFICATION

D03114

Adjustable Torque Screwdriver

EN#:4711552156232



Safety and environmental protection :

- RoHS & Pb free: RoHS

Material :

- Material of hex drive: Chrome vanadium steels SAE(AISI) 6140
- Material of adjustment ring & body: Aluminum alloy
- Material of handle: NBR Rubber

Specifications :

- Length (mm): 200
- Specification of torque (Nm): 1~6Nm
- Specification of torque (lbf-in): 13.28~48.68 lbf-in
- Graduation(N-M): 0.1
- Tolerance of torque (%): ±6%
- Dimension of ratchet: 1/4" (6.35mm)

Product Weight (w/o package)(g)	Measurement		
	L(mm)	W(mm)	H(mm)
335.4	200	37	37

Individual Packing :

Master Packing :

	Pieces	N.W.(Kg)	G.W.(Kg)	Measurement			Cuft
				L(cm)	W(cm)	H(cm)	
Individual Packing	1	-	0.435	25.5	6.97	0	-
Inner box	1	0	0	0	0	0	0
CTN	24	10.44	11.34	50.3	29.7	20.3	1.07