



12dB Fixed Mini-Type Attenuator Pad

FAM-12



Nickel-plated, solid brass body, monolithic ceramic printed circuit board, ensuring rugged construction, etched glaze-type resistors provide $\pm 5\%$ accuracy and excellent return loss, small 1.375" size, 22-gauge spring steel center pin, female to male fitting, not DC passive.

Specifications:

Bandwidth: 100KHz~1750MHz

Return loss: 20dB typical

Accuracy: $\pm 5\%$

Package Specifications & Dimensions

Weight:	0.1875 lbs.
Length:	1.25 in.
Width:	0.5 in.
Height:	0.5 in.
