

2mm Digital Multimeter Probe



Description

UL listed Digital Multimeter probe set with 2mm (0.08") diameter probe tip. Connector is a right-angle sheathed 4mm banana plug. Set includes alligator clip pair featuring gold plated pin tip sockets. They mate easily onto the probe tips.

Specifications:

Materials	: Body - PVC/Nylon
Contact	: Brass, Nickel Plated
Banana Contact	: Phosphor Bronze, Nickel Plated
Alligator Clips	: Steel, Nickel Plated
IEC Rating	: 1,000V CAT III
Current	: 12A (Max.)
Resistance	: 30m Ω (Max.)
Jacket Material	: PVC
Conductor Area	: 0.75mm ²
Wire Gauge	: 18 AWG
Stranding	: 195 \times 0.07 (# \times mm)
OD	: 3.7mm (0.146")
Temperature	: -20°C to +80°C

Part Number Table

Description	Part Number
2mm Digital Multimeter Probe	76-108A

Important Notice : This data sheet and its contents (the "Information") belong to the members of the Premier Farnell group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Tenma is the registered trademark of the Group. © Premier Farnell plc 2012.

