

SIMATIC S7-1200, ANALOG INPUT, SM 1231, 4 AI, +/-10V, +/-5V, +/-2.5V, OR 0-20MA/4-20 MA, 12 BIT + SIGN BIT (13 BIT ADC)



### Supply voltage

Rated value (DC)

- 24 V DC

Yes

### Input current

Current consumption, typ.

45 mA

from backplane bus 5 V DC, typ.

80 mA

### Power loss

Power loss, typ.

1.5 W

### Analog inputs

Number of analog inputs

4; Current or voltage differential inputs

permissible input voltage for current input  
(destruction limit), max.

$\pm 35$  V

permissible input voltage for voltage input  
(destruction limit), max.

35 V

permissible input current for voltage input  
(destruction limit), max.

40 mA

permissible input current for current input (destruction  
limit), max.

40 mA

Cycle time (all channels) max.	625 $\mu$ s
<b>Input ranges</b>	
• Voltage	Yes; $\pm 10V$ , $\pm 5V$ , $\pm 2.5V$
• Current	Yes; 4 to 20 mA, 0 to 20 mA
• Thermocouple	No
• Resistance thermometer	No
• Resistance	No
<b>Input ranges (rated values), voltages</b>	
• -10 V to +10 V	Yes
• Input resistance (-10 V to +10 V)	$\geq 9$ MOhm
• -2.5 V to +2.5 V	Yes
• Input resistance (-2.5 V to +2.5 V)	$\geq 9$ MOhm
• -5 V to +5 V	Yes
• Input resistance (-5 V to +5 V)	$\geq 9$ MOhm
<b>Input ranges (rated values), currents</b>	
• 0 to 20 mA	Yes
• Input resistance (0 to 20 mA)	280 $\Omega$
• 4 mA to 20 mA	Yes
<b>Analog value generation</b>	
<b>Integration and conversion time/resolution per channel</b>	
• Resolution with overrange (bit including sign), max.	12 bit; + sign
• Integration time, parameterizable	Yes
• Interference voltage suppression for interference frequency f1 in Hz	40 dB, DC to 60 V for interference frequency 50 / 60 Hz
<b>Smoothing of measured values</b>	
• parameterizable	Yes
• Step: None	Yes
• Step: low	Yes
• Step: Medium	Yes
• Step: High	Yes
<b>Errors/accuracies</b>	
Temperature error (relative to input range), (+/-)	25 $^{\circ}$ C $\pm 0.1\%$ , to 55 $^{\circ}$ C $\pm 0.2\%$ total measurement range
<b>Basic error limit (operational limit at 25 <math>^{\circ}</math>C)</b>	
• Voltage, relative to input area, (+/-)	0.1 %
• Current, relative to input area, (+/-)	0.1 %
<b>Interference voltage suppression for <math>f = n \times (f1 \pm 1 \%)</math>, f1 = interference frequency</b>	
• Common mode voltage, max.	12 V
<b>Interrupts/diagnostics/status information</b>	
Alarms	Yes
Diagnostic functions	Yes

Alarms	
• Diagnostic alarm	Yes
Diagnostic messages	
• Monitoring the supply voltage	Yes
• Wire-break	Yes
Diagnostics indication LED	
• for status of the inputs	Yes
• for maintenance	Yes
Degree and class of protection	
Degree of protection acc. to EN 60529	
• IP20	Yes
Standards, approvals, certificates	
CE mark	Yes
CSA approval	Yes
FM approval	Yes
RCM (formerly C-TICK)	Yes
Marine approval	
• Marine approval	Yes
Ambient conditions	
Free fall	
• Fall height, max.	0.3 m; five times, in dispatch package
Ambient temperature during operation	
• permissible temperature range	-20 °C to +60 °C horizontal mounting, -20 °C to 50 °C vertical mounting, 95% humidity, non-condensing
• min.	-20 °C
• max.	60 °C
Ambient temperature during storage/transportation	
• min.	-40 °C
• max.	70 °C
Air pressure acc. to IEC 60068-2-13	
• Operation, min.	795 hPa
• Operation, max.	1 080 hPa
• Storage/transport, min.	660 hPa
• Storage/transport, max.	1 080 hPa
Relative humidity	
• permissible range (without condensation) at 25 °C	95 %
Extended ambient conditions	
Pollutant concentrations	
— SO <sub>2</sub> at RH < 60% without condensation	SO <sub>2</sub> : < 0.5 ppm; H <sub>2</sub> S: < 0.1 ppm; RH < 60% condensation-free
Connection method	

required front connector	Yes
--------------------------	-----

### Mechanics/material

Enclosure material (front)	
• Plastic	Yes

### Dimensions

Width	45 mm
Height	100 mm
Depth	75 mm

### Weights

Weight, approx.	180 g
-----------------	-------

**last modified:** 22.01.2016