


Insulated FLEX-DOT screwdrivers to VDE-Standard

Insulated VDE screwdrivers for work on or around live components up to 1,000V AC. Injection of the protective insulation onto the screwdriver blade and piece by piece inspection offer maximum safety.


PROXXON
INDUSTRIAL




Insulated slotted screwdrivers



NO	mm	mm	mm	mm
22 300	2.5	0.4	75	75
22 304	4	0.8	100	100
22 306	5.5	1	125	100
22 308	6.5	1.2	150	110



Insulated PHILLIPS screwdrivers



NO	PH	mm	mm
22 330	0	60	75
22 332	1	80	100
22 334	2	100	110

6-piece insulated VDE screwdriver set

NO	Contents				
22 630	4x Slot	2.5	4	5.5	6.5
	2 x PH	PH 1	PH 2		



Voltage tester as per VDE 0680

Indication of voltage between phases 220 to 250V, 50/60Hz (up to 500Hz). Of high-strength ABS, with roughened, non-slip surface. Tested piece by piece at 2,000V. Blade length 60mm. Total length 140mm.

NO	mm	mm	mm	mm
22 390	3	0.5	65	75







2 year guarantee

For full professional use!

Precision screwdrivers for electronic engineers, camera builders, watchmakers, jewellers, precision engineers and model makers.

15-piece MICRO-Driver set

Blades of high alloy nickel-chrome-molybdenum steel (SAE 8660) for maximum hardness and toughness. Chrome-plated with brinelled tip. With ergonomically formed two-component handle of high-quality plastic (impact as well as oil and acid resistant) with soft component in the finger grip area. The revolving top and finger mould improve easy of use.

-  Slot: 1 x 50 – 2 x 50 – 3 x 50
-  Phillips: PH 0-3 x 50 – PH 0 x 50 – PH 1-2 x 50
-  TX: T 5 x 50 – T 6 x 50 – T 8 x 50 – T 10 x 50 – T 15 x 50
-  HX: 1.5 x 50 – 2 x 50 – 2.5 x 50 – 3 x 50

NO 28 148

