



Safety data sheet according to 1907/2006/EC, Article 31

Printing date 01.04.2016

Revision: 01.04.2016

Identification of the substance/mixture and of the company/undertaking

- **1.1 Product identifier**
- **Trade name:** *Lötdraht HS10 Ecoloy TSC*
- **1.2 Relevant identified uses of the substance or mixture and uses advised against**
No further relevant information available.
- **Application of the substance / the mixture** *Brazing alloy*
- **1.3 Details of the supplier of the safety data sheet**
- **Manufacturer/Supplier:**
*Stannol GmbH
Haberstr. 24
D-42551 Velbert
Deutschland
+49/2051-3120-332
sdb@stannol.de*
- **Further information obtainable from:** *Product Safety Department*
- **1.4 Emergency telephone number:** *8:00 am - 5:00 pm CET +49 (0) 2051 3120 332*

Hazards identification

- **2.1 Classification of the substance or mixture**
- **Classification according to Regulation (EC) No 1272/2008**
The product is not classified according to the CLP regulation.
- **2.2 Label elements**
- **Labelling according to Regulation (EC) No 1272/2008** *Void*
- **Hazard pictograms** *Void*
- **Signal word** *Void*
- **Hazard statements** *Void*
- **Additional information:**
*May cause occupational asthma.
Contains Rosin. May produce an allergic reaction.*
- **2.3 Other hazards**
*Inhalation of vapors that are released during the soldering process is to be avoided. Flux fumes irritate the nose, throat and lungs and may after prolonged or repeated exposure give an allergical reaction (asthma). Therefore, an active exhaust is recommended.
Always wash after handling solder and before eating, drinking and smoking hands with soap and water.
Not more than 500 °C heat.
Keep out of the reach of children.
May cause occupational asthma*
- **Results of PBT and vPvB assessment**
- **PBT:** *Not applicable.*
- **vPvB:** *Not applicable.*

Composition/information on ingredients

- **3.2 Mixtures**
- **Description:** *Mixture of substances listed below with nonhazardous additions.*
- **Dangerous components:**
CAS: 7440-22-4 silver 2-9%
EINECS: 231-131-3 substance with a Community workplace exposure limit

(Contd. on page 2)
GB



Safety data sheet according to 1907/2006/EC, Article 31

Printing date 01.04.2016

Revision: 01.04.2016

Trade name: Lötdraht HS10 Ecoloy TSC

CAS: 8050-09-7	Rosin	(Contd. of page 1)
EINECS: 232-475-7	⚠ Skin Sens. 1, H317	≤ 2.5%
CAS: 7440-31-5	tin	80-100%
EINECS: 231-141-8		
CAS: 7440-50-8	copper	≤ 2.5%
EINECS: 231-159-6	substance with a Community workplace exposure limit	
CAS: 7439-92-1	lead	≤ 0.1%
EINECS: 231-100-4	⚠ Repr. 1A, H360; STOT RE 2, H373; ⚠ Acute Tox. 4, H302; Acute Tox. 4, H332	

· **Additional information:** For the wording of the listed hazard phrases refer to section 16.

First aid measures

- **4.1 Description of first aid measures**
- **General information:** No special measures required.
- **After inhalation:** Supply fresh air; consult doctor in case of complaints.
- **After skin contact:** Generally the product does not irritate the skin.
- **After eye contact:** Rinse opened eye for several minutes under running water.
- **After swallowing:** If symptoms persist consult doctor.
- **4.2 Most important symptoms and effects, both acute and delayed** No further relevant information available.
- **4.3 Indication of any immediate medical attention and special treatment needed**
No further relevant information available.

Firefighting measures

- **5.1 Extinguishing media**
- **Suitable extinguishing agents:**
CO₂, powder or water spray. Fight larger fires with water spray or alcohol resistant foam.
- **5.2 Special hazards arising from the substance or mixture** No further relevant information available.
- **5.3 Advice for firefighters**
- **Protective equipment:** No special measures required.

Accidental release measures

- **6.1 Personal precautions, protective equipment and emergency procedures** Not required.
- **6.2 Environmental precautions:** Do not allow to enter sewers/ surface or ground water.
- **6.3 Methods and material for containment and cleaning up:** Pick up mechanically.
- **6.4 Reference to other sections**
See Section 7 for information on safe handling.
See Section 8 for information on personal protection equipment.
See Section 13 for disposal information.

Handling and storage

- **7.1 Precautions for safe handling** No special measures required.
- **Information about fire - and explosion protection:** No special measures required.

(Contd. on page 3)

GB



Safety data sheet according to 1907/2006/EC, Article 31

Printing date 01.04.2016

Revision: 01.04.2016

Trade name: Lötdraht HS10 Ecoloy TSC

(Contd. of page 2)

- **7.2 Conditions for safe storage, including any incompatibilities**
- **Storage:**
- **Requirements to be met by storerooms and receptacles:** No special requirements.
- **Information about storage in one common storage facility:** Not required.
- **Further information about storage conditions:** None.
- **7.3 Specific end use(s)** No further relevant information available.

Exposure controls/personal protection

- **Additional information about design of technical facilities:** No further data; see item 7.
- **8.1 Control parameters**
- **Ingredients with limit values that require monitoring at the workplace:**
The following constituents are the only constituents of the product which have a PEL, TLV or other recommended exposure limit.
At this time, the other constituents have no known exposure limits.
- **7440-22-4 silver**
WEL Long-term value: 0.1 mg/m³
- **8050-09-7 Rosin**
WEL Short-term value: 0.15 mg/m³
Long-term value: 0.05 mg/m³
Sen
- **7440-50-8 copper**
WEL Short-term value: 2** mg/m³
Long-term value: 0.2* 1** mg/m³
*fume **dusts and mists (as Cu)
- **Additional information:** The lists valid during the making were used as basis.
- **8.2 Exposure controls**
- **Personal protective equipment:**
- **General protective and hygienic measures:**
The usual precautionary measures are to be adhered to when handling chemicals.
- **Respiratory protection:** Not required.
- **Protection of hands:**
Rubber gloves
Synthetic rubber gloves
To avoid skin problems reduce the wearing of gloves to the required minimum.
- **Material of gloves**
The selection of the suitable gloves does not only depend on the material, but also on further marks of quality and varies from manufacturer to manufacturer. As the product is a preparation of several substances, the resistance of the glove material can not be calculated in advance and has therefore to be checked prior to the application.
- **Penetration time of glove material**
The exact break through time has to be found out by the manufacturer of the protective gloves and has to be observed.
- **Eye protection:** Not required.

GB

(Contd. on page 4)



Safety data sheet according to 1907/2006/EC, Article 31

Printing date 01.04.2016

Revision: 01.04.2016

Trade name: Lötdraht HS10 Ecoloy TSC

(Contd. of page 3)

Physical and chemical properties

· 9.1 Information on basic physical and chemical properties

· General Information

· Appearance:

Form: Rope

Colour: Grey

· Odour: Characteristic

· Odour threshold: Not determined.

· pH-value: Not applicable.

· Change in condition

Melting point/Melting range: Undetermined.

Boiling point/Boiling range: Undetermined.

· Flash point: Not applicable.

· Flammability (solid, gaseous): Not determined.

· Ignition temperature:

Decomposition temperature: Not determined.

· Self-igniting: Product is not selfigniting.

· Danger of explosion: Product does not present an explosion hazard.

· Explosion limits:

Lower: Not determined.

Upper: Not determined.

· Vapour pressure: Not applicable.

· Density: Not determined.

· Relative density: Not determined.

· Vapour density: Not applicable.

· Evaporation rate: Not applicable.

· Solubility in / Miscibility with water:

Insoluble.

· Partition coefficient (n-octanol/water): Not determined.

· Viscosity:

Dynamic: Not applicable.

Kinematic: Not applicable.

· Solvent content:

Organic solvents: 0.0 %

VOC (EC) 0.00 %

Solids content: 100.0 %

· 9.2 Other information: No further relevant information available.

Stability and reactivity

· 10.1 Reactivity: No further relevant information available.

(Contd. on page 5)

GB



Safety data sheet according to 1907/2006/EC, Article 31

Printing date 01.04.2016

Revision: 01.04.2016

Trade name: Lötdraht HS10 Ecoloy TSC

(Contd. of page 4)

- **10.2 Chemical stability**
- **Thermal decomposition / conditions to be avoided:** No decomposition if used according to specifications.
- **10.3 Possibility of hazardous reactions** No dangerous reactions known.
- **10.4 Conditions to avoid** No further relevant information available.
- **10.5 Incompatible materials:** No further relevant information available.
- **10.6 Hazardous decomposition products:** No dangerous decomposition products known.

Toxicological information

- **11.1 Information on toxicological effects**
- **Acute toxicity** Based on available data, the classification criteria are not met.
- **Primary irritant effect:**
- **Skin corrosion/irritation** Based on available data, the classification criteria are not met.
- **Serious eye damage/irritation** Based on available data, the classification criteria are not met.
- **Respiratory or skin sensitisation** Based on available data, the classification criteria are not met.
- **Sensitisation** May cause occupational asthma
- **CMR effects (carcinogenicity, mutagenicity and toxicity for reproduction)**
- **Germ cell mutagenicity** Based on available data, the classification criteria are not met.
- **Carcinogenicity** Based on available data, the classification criteria are not met.
- **Reproductive toxicity** Based on available data, the classification criteria are not met.
- **STOT-single exposure** Based on available data, the classification criteria are not met.
- **STOT-repeated exposure** Based on available data, the classification criteria are not met.
- **Aspiration hazard** Based on available data, the classification criteria are not met.

Ecological information

- **12.1 Toxicity**
- **Aquatic toxicity:** No further relevant information available.
- **12.2 Persistence and degradability** No further relevant information available.
- **12.3 Bioaccumulative potential** No further relevant information available.
- **12.4 Mobility in soil** No further relevant information available.
- **Additional ecological information:**
- **General notes:**
Water hazard class 1 (German Regulation) (Self-assessment): slightly hazardous for water
Do not allow undiluted product or large quantities of it to reach ground water, water course or sewage system.
- **12.5 Results of PBT and vPvB assessment**
- **PBT:** Not applicable.
- **vPvB:** Not applicable.
- **12.6 Other adverse effects** No further relevant information available.

Disposal considerations

- **13.1 Waste treatment methods**
- **Recommendation** Smaller quantities can be disposed of with household waste.
- **Uncleaned packaging:**
- **Recommendation:** Disposal must be made according to official regulations.

GB
(Contd. on page 6)



Safety data sheet
according to 1907/2006/EC, Article 31

Printing date 01.04.2016

Revision: 01.04.2016

Trade name: **Lötdraht HS10 Ecoloy TSC**

(Contd. of page 5)

Transport information

- **14.1 UN-Number**
- **ADR, ADN, IMDG, IATA** not regulated

- **14.2 UN proper shipping name**
- **ADR, ADN, IMDG, IATA** not regulated

- **14.3 Transport hazard class(es)**
- **ADR, ADN, IMDG, IATA**
- **Class** not regulated

- **14.4 Packing group**
- **ADR, IMDG, IATA** not regulated

- **14.5 Environmental hazards:** Not applicable.

- **14.6 Special precautions for user** Not applicable.

- **14.7 Transport in bulk according to Annex II of Marpol and the IBC Code** Not applicable.

- **UN "Model Regulation":** not regulated

Regulatory information

- **15.1 Safety, health and environmental regulations/legislation specific for the substance or mixture**
- **Directive 2012/18/EU**
- **Named dangerous substances - ANNEX I** None of the ingredients is listed.
- **15.2 Chemical safety assessment:** A Chemical Safety Assessment has not been carried out.

Other information

This information is based on our present knowledge. However, this shall not constitute a guarantee for any specific product features and shall not establish a legally valid contractual relationship.

- **Relevant phrases**
H302 Harmful if swallowed.
H317 May cause an allergic skin reaction.
H332 Harmful if inhaled.
H360 May damage fertility or the unborn child.
H373 May cause damage to organs through prolonged or repeated exposure.

- **Department issuing SDS:** Product Safety Department
- **Contact:** Hr. Dörr
- **Abbreviations and acronyms:**
ADR: Accord européen sur le transport des marchandises dangereuses par Route (European Agreement concerning the International Carriage of Dangerous Goods by Road)
IMDG: International Maritime Code for Dangerous Goods
IATA: International Air Transport Association
GHS: Globally Harmonised System of Classification and Labelling of Chemicals
EINECS: European Inventory of Existing Commercial Chemical Substances
ELINCS: European List of Notified Chemical Substances
CAS: Chemical Abstracts Service (division of the American Chemical Society)
VOC: Volatile Organic Compounds (USA, EU)
LD50: Lethal dose, 50 percent
PBT: Persistent, Bioaccumulative and Toxic

(Contd. on page 7)
GB



STANNOL

Page 7/7

Safety data sheet
according to 1907/2006/EC, Article 31

Printing date 01.04.2016

Revision: 01.04.2016

Trade name: Lötdraht HS10 Ecoloy TSC

(Contd. of page 6)

vPvB: very Persistent and very Bioaccumulative

LC50: Lethal concentration, 50 percent

SVHC: Substances of Very High Concern

Acute Tox. 4: Acute toxicity – Category 4

Skin Sens. 1: Skin sensitisation – Category 1

Repr. 1A: Reproductive toxicity – Category 1A

STOT RE 2: Specific target organ toxicity (repeated exposure) – Category 2

GB