

Modular Plug RJ45 (8P8C)



Modular Plug (P88FB15 + P88FB50 + P88RB15 + P88RB50 + P88RB50S)

8 position 8 contact plug used mainly for data cabling systems (eg Category 3, 4 and 5e). Known mainly as RJ45 connector but also used in RJ48 and RJ61 applications.

Features

- Suitable for round or flat cable
- UL listed
- Contact blades are suitable for stranded and/or solid wire from 24-26 AWG
- Available for UTP (unshielded) and FTP (shielded) cable
- Also available in keyed version known as RJ45S (PCU88k) and 10 position 10 contact versions known as RJ50 (PCW1010 and PGW1010) see 'Other Modular Plugs'
- Customised logos and colours are available to order

Specifications

- Housing: Polycarbonate, UL94V
- Contacts: Available in 15µ"/0.38µm and 50µ"/1.27µm gold plating over 100u" / 2.54µm Nickel plate over Phosphor Bronze





