



How to order:



Contents

■ Connecting to the future	6
■ Standard Type PCB Terminal Blocks	8
■ Rising Clamp PCB Terminal Blocks	14
■ Pluggable Terminal Blocks - Headers	26
■ Pluggable Terminal Blocks - Plugs	38
■ Screwless Terminal Blocks	54



Abstand/Winkel	Pas	Passo	Paso	Шаг
Technische Daten	Caractéristiques techniques	Dati tecnici	Datos técnicos	Технические характеристики
Nennspannung	Tension nominale	Tensione nominale	Voltaje nominal	Номинальное напряжение
Nennstrom	Courant nominal	Corrente nominale	Corriente nominal	Номинальный ток
Kabelbereich	Calibre de fils	Gamma fili	Gama de cables	Сечение провода
Nennstoßspannung	Sur-tension nominale	Sovratensione nominale	Voltaje de sobretensión nominal	Доступные опции
Schraube	Vis	Vite	Tornillo	Винт
Pol	Pôle	Polarità	Polo	Полюс

Abstand/Winkel	Pas	Passo	Paso	Шаг
Technische Daten	Caractéristiques techniques	Dati tecnici	Datos técnicos	Технические характеристики
Nennspannung	Tension nominale	Tensione nominale	Voltaje nominal	Номинальное напряжение
Nennstrom	Courant nominal	Corrente nominale	Corriente nominal	Номинальный ток
Kabelbereich	Calibre de fils	Gamma fili	Gama de cables	Сечение провода
Nennstoßspannung	Sur-tension nominale	Sovratensione nominale	Voltaje de sobretensión nominal	Доступные опции
Schraube	Vis	Vite	Tornillo	Винт
Pol	Pôle	Polarità	Polo	Полюс



	20.920M	21.920M	20.920MF	21.920MF	21.951ML	21.951MLF	21.950MT	21.950MTF	20.970M	21.970M
Pitch	5.00mm (5.08mm)		5.00mm (5.08mm)		5.08mm		5.08mm		5.00mm (5.08mm)	
Technical Data	UL	IEC	UL	IEC	UL	IEC	UL	IEC	UL	IEC
Rated voltage	300V	600V	300V	600V	300V	600V	300V	600V	300V	600V
Rated current	15A	18A	15A	18A	12A	14A	12A	14A	15A	18A
Wire range	0.2-2.5mm ² / 30 - 12 AWG		0.2-2.5mm ² / 30 - 12 AWG		0.2-1.5 mm ² / 30-14 AWG		0.2-1.5 mm ² / 30-14 AWG		0.2-2.5mm ² / 30 - 12 AWG	
Available options	300V/15A 320V/20A		300V/15A 320V/20A				30-12 AWG		300V/15A 320V/20A	
Screw	M2.5		M2.5		M2		M2.5		M2.5	
Available poles	2 - 24		2 - 24		2 - 24		2 - 12 (with twin connection)		2 - 24	



	20.970MF	21.970MF	21.970ML	21.970MLF	20.954M	21.954M	20.954MF	21.954MF	20.960M	21.960M	20.960MF	21.960MF
Pitch	5.00mm (5.08mm)		5.08mm		5.08mm		5.00mm (5.08mm)		7.50mm (7.62mm)		7.50mm (7.62mm)	
Technical Data	UL	IEC	UL	IEC	UL	IEC	UL	IEC	UL	IEC	UL	IEC
Rated voltage	300V	600V	300V	600V	300V	600V	300V	600V	300V	750V	300V	750V
Rated current	15A	18A	12A	14A	12A	14A	15A	18A	15A	17.5A	15A	17.5A
Wire range	0.2-2.5mm ² / 30 - 12 AWG		0.2-1.5 mm ² / 28-14 AWG		0.2-1.5 mm ² / 28-14 AWG		0.2-2.5 mm ² / 28 - 12 AWG		0.5-2.5 mm ² / 28 - 12 AWG		0.5-2.5 mm ² / 28 - 12 AWG	
Available options	300V/15A 320V/20A						300V/15A 320V/20A		300V/15A 320V/20A		300V/15A 320V/20A	
Screw	M2.5		M2		M2		M2.5		M2.5		M2.5	
Available poles	2 - 24		2 - 24		2 - 24		2 - 24		2 - 12		2 - 12	