


How to order:




Contents

■ Connecting to the future	6
■ Standard Type PCB Terminal Blocks	8
■ Rising Clamp PCB Terminal Blocks	14
■ Pluggable Terminal Blocks - Headers	26
■ Pluggable Terminal Blocks - Plugs	38
■ Screwless Terminal Blocks	54



Abstand/Winkel	Pas	Passo	Paso	Шаг
Technische Daten	Caractéristiques techniques	Dati tecnici	Datos técnicos	Технические характеристики
Nennspannung	Tension nominale	Tensione nominale	Voltaje nominal	Номинальное напряжение
Nennstrom	Courant nominal	Corrente nominale	Corriente nominal	Номинальный ток
Kabelbereich	Calibre de fils	Gamma fili	Gama de cables	Сечение провода
Nennstoßspannung	Sur-tension nominale	Sovratensione nominale	Voltaje de sobretensión nominal	Доступные опции
Schraube	Vis	Vite	Tornillo	Винт
Pol	Pôle	Polarità	Polo	Плюс



Abstand/Winkel	Pas	Passo	Paso	Шаг
Technische Daten	Caractéristiques techniques	Dati tecnici	Datos técnicos	Технические характеристики
Nennspannung	Tension nominale	Tensione nominale	Voltaje nominal	Номинальное напряжение
Nennstrom	Courant nominal	Corrente nominale	Corriente nominal	Номинальный ток
Kabelbereich	Calibre de fils	Gamma fili	Gama de cables	Сечение провода
Nennstoßspannung	Sur-tension nominale	Sovratensione nominale	Voltaje de sobretensión nominal	Доступные опции
Schraube	Vis	Vite	Tornillo	Винт
Pol	Pôle	Polarità	Polo	Плюс



	20.1550M	21.1550M	20.1550MF	21.1550MF	20.1500M	21.1500M	20.1500MF	21.1500MF	20.1510M	21.1510M	20.1510MF	21.1510MF	21.1570M	
	 $3.50 \times (P-1) + 4.3$ $(3.81 \times (P-1) + 4.6)$		 $3.50 \times (P-1) + 14.1$ $(3.81 \times (P-1) + 14.4)$		 $3.50 \times (P-1) + 4.3$ $(3.81 \times (P-1) + 4.6)$		 $3.50 \times (P-1) + 14.00$ $(3.81 \times (P-1) + 14.40)$		 $3.50 \times (P-1) + 4.30$ $(3.81 \times (P-1) + 4.60)$		 $3.50 \times (P-1) + 14.00$ $(3.81 \times (P-1) + 14.40)$		 $3.81 \times (P-1) + 2.30 \times 2$	
Pitch	3.50mm (3.81mm)													
Technical Data	UL	IEC	UL	IEC	UL	IEC	UL	IEC	UL	IEC	UL	IEC	UL	IEC
Rated voltage	300V	320V	300V	320V	300V	320V	300V	320V	300V	320V	300V	320V	300V	320V
Rated current	8A	14A	8A	14A	8A	14A	8A	14A	8A	14A	8A	14A	8A	14A
Wire range	0.2-1.5mm ² / 28 - 14 AWG													
Available options	300V/8A	250V/10A	300V/8A	250V/10A	300V/8A	250V/10A	300V/8A	250V/10A	300V/8A	250V/10A	300V/8A	250V/10A	300V/8A	250V/10A
Screw	M2													
Available poles	2 - 24		2 - 24		2 - 22		2 - 20		2 - 22		2 - 20		2 - 24	



	21.1570MF	20.950M	21.950M	20.950MF	21.950MF	20.951M	21.950MC	20.910M	21.910M	20.910MF	21.910MF	
	 4.80 , $3.81 \times (P-1) + 4.60$, 4.80		 $5.00 \times P$ $(5.08 \times P)$		 $5.00 \times P + 10.00$ $(5.08 \times P + 10.16)$		 $5.00 \times P$		 $5.00 \times P$ $(5.08 \times P)$		 $5.00 \times (P-1) + 15.00$ $(5.08 \times (P-1) + 15.24)$	
Pitch	3.81mm		5.00mm (5.08mm)		5.00mm (5.08mm)		5.00mm		5.00mm (5.08mm)		5.00mm (5.08mm)	
Technical Data	UL	IEC	UL	IEC	UL	IEC	UL	IEC	UL	IEC	UL	IEC
Rated voltage	300V	320V	300V	600V	300V	600V	300V	600V	300V	600V	300V	600V
Rated current	8A	14A	15A	18A	15A	18A	15A	18A	15A	18A	15A	18A
Wire range	0.2-1.5 mm ² / 30-14 AWG											
Available options			300V/15A	320V/20A	300V/15A	320V/20A			300V/15A	320V/20A	300V/15A	320V/20A
Screw	M2		M2.5		M2.5		M2.5		M2.5		M2.5	
Available poles	2 - 22		2 - 24		2 - 24		2 - 24		2 - 24		2 - 24	