



Main

Commercial Status	Commercialised
Range of product	Harmony XVD Application
Product or component type	Base unit with cover
Component name	XVD
Indicator bank base type	Standard
Material	Polycarbonate cover unit Glass reinforced polyamide base unit

Complementary

Fixing mode	Direct or tube fixing
Mounting diameter	70 mm
Product destination	Banks without flash discharge tube unit
Cable entry	Bottom entry
Assembly style	Customer assembly, up to 5 units
Terminals description ISO n°1	(COM-1)PW (COM-2)PW (COM-3)PW (COM-4)PW (COM-5)PW (GND)GROUND
Product weight	0.18 kg

Environment


Product certifications	CSA GOST UL
Standards	EN/IEC 60947-5-1
Protective treatment	TC
Ambient air temperature for storage	-40...70 °C
IP degree of protection	IP40 IEC 60529

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Customer Assembled Indicator Bank without “Flash” Discharge Tube

Dimensions

Below drawing shows the minimum configuration of the product. Select the number of stages according to the product characteristics in order to get b dimension.



- (1) Base unit
- (2) Illuminated unit XVDC3•/C4•• or audible unit XVDC9•, to be ordered separately
- (3) Cover (included with base unit)

Number of illuminated or audible signalling units (no “flash”)	b in mm	b in in.
1	140	5.51
2	203	7.99
3	266	10.47
4	329	12.95
5	392	15.43

Customer Assembled Beacons and Indicator Banks

Wiring Diagrams

