



ESQT-125-02-L-Q-465 ESQT-115-02-GF-D-600 ESQT-125-03-M-Q-310 **ESQT SERIES**

(2,00 mm) .0787"

E ELEVATED SOCKET STRIPS

SPECIFICATIONS

For complete specifications see www.samtec.com?ESQT

Insulator Material: Black Liquid Crystal Polymer Contact Material: Phosphor Bronze Plating:

Sn or Au over 50μ" (1,27 μm) Ni Current Rating (ESQT/TMMH): 4.5 A per pin

4.5 A per pin (1 pin powered per row) Operating Temp Range: -55°C to +125°C Contact Resistance: 10 mΩ

Insertion Depth: (2,62 mm) .103" to (5,03 mm) .198" with (0,38 mm) .015" wipe

Max Cycles: 100 with 10μ" (0,25 μm) Au Insertion Force:

(Single contact only) 4 oz (1,11 N) avg. Withdrawal Force: (Single contact only) 3 oz (0,83 N) avg.

RoHS Compliant: Yes Lead-Free Solderable: Yes, for -S, -D & -Q (Wave only for -T, -5 & -6)

RECOGNITIONS

For complete scope of recognitions see www.samtec.com/quality






Other Solutions

Surface Mount See SQW and **TLE Series**

Low **Profile** See CLT Series.







Mates with:

TMMH, TMM MTMM, MMT, TW LTMM, ZLTMM, ESQT, TCMD, PTT, TSH, TMMS



(2,00 mm) .0787" pitch High Retention Contacts

APPLICATION SPECIFIC OPTION: NOTEBOOK 2.5" DISK DRIVE INTERFACE



Note: This Series is non-standard, non-returnable,

ESQT



NO. PINS PER ROW



PLATING OPTION

ROW OPTION

BODY HEIGHT

OTHER OPTION

02 thru 50

No. of positions x (2,00) .0787 + (0,30) .012

Specify LEAD STYLE from

chart

Gold flash on contact. Matte Tin on tail

> = 10µ" (0,25 µm) Gold on contact, Matte Tin on tail

> –M = 20µ" (0,51 µm) Gold on contact, Matte Tin on tail

–GF = 15µ" (0,38 µm) Gold on contact, Gold flash on tail (Recommended for self-nesting) (-02 lead style only)

-S = Single Row

–D = Double Row

-Т = Triple Row

-Q = Quad Row

-5 = Five Row

> -6= Six Row

"XXX" = Body Height (in inches)

(7,87 mm) .310" minimum for -S, -D, -Q

(9,53 mm) .375" minimum for -T, -5, -6

"XXX" = Polarized **Position** (Indicate position


number)

OTHER SOLUTIONS



Paste In Hole (PIH) processing. Contact Samtec ASP Group. (Not recommended for stack through applications)

LEAD	Α	MAX	MAX BODY
STYLE		TAIL	HEIGHT
-02	(21,59)	(13,72)	(20,32)
	.850	.540	.800
-03	(11,63)	(3,76)	(10,36)
	.458	.148	.408



.0787 rows

x (2,00) .0787

06