

UNITEST DR 100

Rotary Field Indicator

Technical Data

Voltage Range	200...440 V
Current Consumption (at Voltage)	< 3.5 mA (440 V)
Frequency Range	45...65 Hz
Operation Time	continuous
Pollution Degree	2
Measurement category	CAT III, 400 V
Safety Complying with	IEC61010/EN61010 IEC61557-7/EN61557-7
Power Supply	from unit under test
Dimensions	110 x 58 x 24 mm
Weight	approx. 150 g



Key Functions

- Indication of the three phases via glow lamp
- Indication of the phase rotation direction via glow lamp

General Information

- Swift determination of the phase sequence in three-phase networks

Order Information:

Description	Cat. No.
UNITEST DR 100	9042
Accessory Set UNIdreh	1324
Carrying Case	1150
Clamp-type test probe for Current Tracks	
red	391511
black	391512

Accessories:



Accessory Set UNIdreh
Cat. No. 1324



Carrying Case
Cat. No. 1150



Clamp-type test probe for Current Tracks
Cat. No. 391511 (red)
Cat. No. 391512 (black)



Scope of Supply:

- 1 pc UNITESt DR 100
- 3 pc Test Probes
- 1 pc Crocodile Clamp
- 1 pc Instruction Manual