

Keysight Technologies

CXA X-Series Signal Analyzer, Multi-touch N9000B

Configuration Guide

This configuration guide will help you determine which performance options, measurement applications, accessories, and services to include with your new multi-touch CXA or to add as upgrades to an existing CXA.



Configure Your Keysight CXA Signal Analyzer

This step-by-step process will help you configure your new CXA X-Series signal analyzer. Tailor the performance to meet your requirements.

Included in base product

Standard options and accessories come with the CXA base model at no additional charge and do not need to be ordered. They include:

- Spectrum analyzer measurement application
- Dual-core, high-performance processor, 8 GB RAM, removable solid-state drive
- Frequency reference
- 10 MHz analysis bandwidth
- Enhanced phase noise
- Windows Embedded Standard 7
- Benchtop configuration
- Mouse
- User guide
- Power cord
- 3-year return-to-Keysight warranty

Get More Information

For a summary of specifications, refer to the N9000B CXA data sheet (literature number 5992-1274EN).

A full set of specifications are available in the N9000B CXA Signal Analyzer Specification Guide at www.keysight.com/find/cxa_specifications.

Step 1. Select maximum frequency range (required option; frequency range not upgradeable)

Description	Option number	Additional information
Frequency range, 9 kHz to 3.0 GHz	N9000B-503	
Frequency range, 9 kHz to 7.5 GHz	N9000B-507	
Frequency range, 9 kHz to 13.6 GHz	N9000B-513	
Frequency range, 9 kHz to 26.5 GHz	N9000B-526	

Step 2. Add a preamplifier

Description	Option number	Additional information: Preamplifiers improve the noise floor for low-level signal detection; +20 dB: 100 kHz to 26.5 GHz
Preamplifier, 100 kHz to 3.0 GHz	N9000B-P03	Compatible with N9000B-503, N9000B-507, N9000B-513, and N9000B-526
Preamplifier, 100 kHz to 7.5 GHz	N9000B-P07	Compatible with N9000B-507, N9000B-513, and N9000B-526
Preamplifier, 100 kHz to 13.6 GHz	N9000B-P13	Compatible with N9000B-513 and N9000B-526
Preamplifier, 100 kHz to 26.5 GHz	N9000B-P26	Compatible with N9000B-526

Step 3. Choose frequency reference

Description	Option number	Additional information
Frequency reference	Standard	Aging rate: $\pm 1 \times 10^{-6}$ /year
Precision frequency reference	N9000B-PFR	Reduces frequency drift for more accurate measurements; aging rate: $\pm 1 \times 10^{-7}$ /year

Step 4. Choose an attenuator

Description	Option number	Additional information
Mechanical attenuator	Standard	10 dB steps, 0 to 50 dB, for N9000B-503 and N9000B-507 10 dB steps, 0 to 70 dB, for N9000B-513 and N9000B-526
Fine resolution step attenuator	N9000B-FSA	Allows 2 dB steps for the full range of the attenuator

Step 5. Choose analysis bandwidth

Description	Option number	Additional information
10 MHz analysis bandwidth	Standard	Useful for most 2G and 3G measurement applications
25 MHz analysis bandwidth	N9000B-B25	Extends the analysis (demod) bandwidth from 10 to 25 MHz; useful for most cellular communications, wireless connectivity, and audio/video broadcasting measurement applications

Configure Your Keysight CXA Signal Analyzer (Continued)

Step 6. Add a tracking generator

Description	Option number	Additional information
Tracking generator, 9 kHz to 3.0 GHz	N9000B-T03	Compatible with N9000B-503, N9000B-507 only
Tracking generator, 9 kHz to 6.0 GHz	N9000B-T06	Compatible with N9000B-507 only

Step 7. Add a 75 Ω input connector

Description	Option number	Additional information
Connector, 75 Ω additional RF input, 1.5 GHz	N9000B-C75	Not compatible with Options T03 or T06; compatible with N9000B-503 and N9000B-507 only

Step 8. Choose performance

Description	Option number	Additional information
Enhanced phase noise	Standard	Installed as N9000B-EP4

Step 9. Add optional features

Description	Option number	Additional information
Enhanced display package	N9000B-EDP	Includes spectrogram, trace zoom, and zone span
Basic precompliance EMI	N9000B-EMC	Perform EMI precompliance measurements with CISPR 16-1-1 detectors and bandwidths; tune and listen, and measure at marker are also available
External source control	N9000B-ESC	External source control for Keysight EXG, MXG, and PSG signal generators; includes 3 BNC cables and 1 cross-over LAN cable; compatible with N9000B-503 and N9000B-507 only

Step 10. Choose operating system

Description	Option number	Additional information
Windows Embedded Standard 7	Standard	Installed as N9000B-W7X

Step 11. Add security features

Description	Option number	Additional information
Additional, removable solid-state drive	N9000B-SSD	Provides a fully-imaged, removable solid-state drive in addition to the one installed in the instrument
Exclude launch program	N9000B-SF1	Prevents the launching of Windows programs from the instrument application
Prohibit saving results	N9000B-SF2	Prevents the saving/recall of measurement results or user configurations to/from instrument's data storage

Step 12. Add rear panel output utilities

Description	Option number	Additional information
Second IF output	N9000B-CR3	Wideband IF out; output on Aux IF connector at rear panel; compatible with N9000B-503 and N9000B-507 only

Configure Your Keysight CXA Signal Analyzer (Continued)

Step 13. Choose measurement application or software and license type

Note: The last two letters of the ordering numbers indicate the license type—FP stands for fixed perpetual, TP for transportable perpetual; it is recommended that you configure each application with the same license type; visit www.keysight.com/find/X-series_transportable for more information about transportable licenses.

Description	Fixed license	Transportable license	Additional information
Cellular communications			
LTE/LTE-Advanced	N9080C-1FP	N9080C-1TP	Standard-based, one-button LTE-FDD measurements
FDD	N9080C-2FP	N9080C-2TP	Standard-based, one-button LTE-Advanced FDD measurements; requires N9080C-1FP/1TP
LTE/LTE-Advanced	N9082C-1FP	N9082C-1TP	Standard-based, one-button LTE-TDD measurements
TDD	N9082C-2FP	N9082C-2TP	Standard-based, one-button LTE-Advanced TDD measurements; requires N9082C-1FP/1TP
W-CDMA/HSPA+	N9073C-1FP	N9073C-1TP	Standard-based, one-button W-CDMA measurements
	N9073C-2FP	N9073C-2TP	Adds HSPA measurements; requires 1FP/1TP
	N9073C-3FP	N9073C-3TP	Adds HSPA+ measurements; requires 1FP/1TP, 2FP/2TP
General purpose			
Spectrum analyzer	Standard	Not available	Traditional spectrum analysis plus many new and enhanced functions; power measurements based on industry specifications
Analog demodulation	N9063C-1FP	N9063C-1TP	Installed as N9063C-2FP or -2TP and N9063C-3FP or -3TP. Adds one-button measurement for AM/FM/PM demodulation with metrics, tune and listen, and AF spectrum; supports audio output (output voltage proportional to frequency deviation). FM Stereo and RDS are included.
Phase noise	W9068C-2FP	W9068C-2TP	One-button phase noise measurements in frequency domain (log plot) and time domain (spot frequency)
Noise figure	N9069C-3FP (requires preamplifier)	N9069C-3TP (requires preamplifier)	Installed as N9069C-1FP or -1TP and N9069C-2FP or -2TP. Adds one-button measurements for noise figure, gain, and related metrics; requires preamplifier to meet specifications; works with Keysight N400xA Series smart noise sources and 346 Series noise sources; supports U7227 Series USB external preamplifiers; includes the advanced NF measurement features including external LO control over GPIB/LAN/USB, multi-stage converter tests with system LO, and manual mode to simulate the legacy NF meter.
MATLAB software	N6171A-M01	Not available	Basic signal analysis package; adds MATLAB software environment and the Instrument Control Toolbox (not upgradeable)
	N6171A-M02	Not available	Standard signal analysis package; includes basic package and adds Communications Toolbox and Signal Processing Toolbox (not upgradeable)
	N6171A-M03	Not available	Advanced signal analysis package; includes standard package and adds Filter Design Toolbox, RF Toolbox, and System Test (not upgradeable)
Pulse	N9067C-1FP	Not available	Characterize pulsed RF signals in the time domain, with phase, frequency and statistical analysis of large pulse sets.
89600 VSA software	Not available	89601B (transportable license is standard)	Industry-leading measurement software for evaluating and troubleshooting signals in R&D; PC-based software supporting more than 40 measurement platforms, plus more than 75 signal standards and modulation types including MIMO analysis; www.keysight.com/find/89600vsa

Configure Your Keysight CXA Signal Analyzer (Continued)


Step 14. Choose physical instrument configuration

Description	Option number	Additional information
Bench top configuration	Standard	Provides two side carrying straps, four rear feet, and four bottom feet with a tilt stand
Portable configuration	N9000B-PRC	Provides a convenient, pivoting carrying handle as well as rubber protective corners and end guards; this configuration is intended for applications requiring more rugged packaging, such as in the field

Step 15. Choose accessories

Description	Option number	Additional information
Mouse, USB interface	Standard	Every CXA is shipped with a USB mouse which enhances the usability of the Windows operating system
User guide	Standard	<ul style="list-style-type: none"> – US – English localization – All user documentation is included in the CXA's embedded, context-sensitive help system and on a CD that is shipped with the instrument – User documentation can be downloaded from: www.keysight.com/find/cxa_manuals
Power cord	Standard	Dependent upon region of use
Rack mount	1CM113A	Adds rack mount flanges to the CXA
Front handles	1CN103A	Adds front handles to the CXA
Rack mount with handles	1CP105A	Adds rack mount flanges and handles to the CXA
Rack slide	1CR013A	Adds a non-tilting rack slide to the CXA
USB DVD-ROM/CD-R/RW drive	1DVR001A	Enhances the usability of the Windows operating system
Mouse, USB interface	1MSE001A	
US 65-key USB keyboard	1KBD001A	Smaller keyboard
Front panel protection cover	N9000B-CVR	
Minimum loss pad, 50 to 75 Ω (type-N to BNC)	MLP001A	<ul style="list-style-type: none"> – 50 Ω type-N male to 75 Ω BNC female adapter – Frequency range: 9 MHz to 2 GHz – Input/output return loss: 20 and 11 dB – Insertion loss: 5.7 dB
USB external preamplifier, 10 MHz to 4 GHz	U7227A	
USB external preamplifier, 0.1 to 26.5 GHz	U7227C	
USB external preamplifier, 2 to 50 GHz	U7227F	

For more information on accessories go to: www.keysight.com/find/accessories



CXA bench top configuration

Configure Your Keysight CXA Signal Analyzer (Continued)

Step 16. Choose warranty length		
Description	Option number	Additional information
Return-to-Keysight warranty, 3 years	Standard	3-year warranty is included at no additional charge
Warranty Assurance Plan, Return-to-Keysight, 5 years	R-51B-001-5Z	
Warranty Assurance Plan, Return-to-Keysight, 7 years	R-51B-001-7Z	
Warranty Assurance Plan, Return-to-Keysight, 10 years	R-51B-001-10Z	

Step 17. Add calibration, technical training, support, and upgrade services		
Description	Option number	Additional information
Commercial calibration certificate with test data	N9000B-UK6	Calibration certificate only available at time of instrument purchase; only provides measurement results
Keysight Cal + uncertainties + guardbanding (accredited cal)	N9000B-AMG	Provides ISO 17025A accredited calibration from factory
ANSI Z540-1-1994 calibration	N9000B-A6J	Provides ANSI Z540 compliant calibration from factory
Calibration Assurance Plan, Return-to-Keysight, 3 years	R-50C-011-3	
Calibration Assurance Plan, Return-to-Keysight, 5 years	R-50C-011-5	Keysight tests your instrument against its original specifications and automatically makes adjustments if outside of specified parameters; pre- and post-adjustment measurement data reports also provided
Calibration Assurance Plan, Return-to-Keysight, 7 years	R-50C-011-7	
Calibration Assurance Plan, Return-to-Keysight, 10 years	R-50C-011-10	
Service: remote scheduled productivity assistance	PS-S10-100	Hourly phone-in technical support service designed to help you understand and operate your equipment through convenient phone and Web access
Service: 1-day start-up assistance	PS-S20-01	Training on how to operate your instrument effectively (recommended)
Service: productivity assistance	PS-S20-100	Daily instrument and application consulting using your equipment and device under test
Service: custom engineering service	PS-X10-100	Application-specific technical assistance

Other calibration options may be available; for more information on calibration go to: www.keysight.com/find/calibration

For more information on training and application support services go to: www.keysight.com/find/training

Instrument Upgrades

Fast license-key upgrades for performance options that do not require additional hardware:

1. Place an order for the upgrade with Keysight and request to receive the option upgrade entitlement certificate and a one-time software upgrade license through email
2. Redeem the certificate through the Web by following the instructions on the certificate
3. Install the license file and latest software in the CXA
4. Begin using the new capability ^{1,2}

Installation and testing information is available at:

www.keysight.com/find/cxa_upgrades

You Can Upgrade!

Options can be added after your initial purchase. Most X-Series options are license-key upgradeable.



Description	Upgrade number	Requirements CXA must already include the following)	Additional information
Increase analysis bandwidth from 10 to 25 MHz	N9000BU-B25	None	
Add preamplifier, 3 GHz	N9000BU-P03	None	
Add preamplifier, 7.5 GHz	N9000BU-P07	507, 513 or 526	Not compatible with Option 503
Add preamplifier, 13.6 GHz	N9000BU-P13	513 or 526	Not compatible with Option 503 or 507
Add preamplifier, 26.5 GHz	N9000BU-P26	526	Not compatible with Option 503, 507, or 513
Add fine resolution step attenuator	N9000BU-FSA	None	
Upgrade to the precision frequency reference	N9000BU-PFR	None	
Add tracking generator, 3 GHz	N9000BU-T03	None	Requires hardware and license key; not compatible with Options 513 or 526
Add tracking generator, 6 GHz	N9000BU-T06	None	Requires hardware and license key; not compatible with Options 503, 513, or 526
Add basic EMI precompliance features	N9000BU-EMC	None	
Add external source control	N9000BU-ESC	None	Adds feature to control the Keysight EXG, MXG, and PSG signal generators; includes 3 BNC cables and 1 cross-over LAN cable; not compatible with Options 513 or 526
Add second IF output	N9000BU-CR3	None	Requires hardware and license key; not compatible with Options 513 or 526
Add enhanced display package	N9000BU-EDP	None	
Add security features, exclude launch program	N9000BU-SF1	None	Prevents the launching of Windows programs from the instrument application
Add security features, prohibit saving results	N9000BU-SF2	None	Prevents the saving/recall of measurement results or user configurations to/from instrument's data storage
Add removable solid state drive	N9000BU-SSD	None	Provides a fully-imaged, removable solid-state drive

1. At the time of manufacture, the hardware related to many of these options was fully adjusted and the option performance was verified to be within its warranted specifications. Within one year of the initial calibration date of the analyzer, this option is fully calibrated with no further adjustment or verification testing.
2. If this analyzer has been adjusted as part of a repair or calibration during its first year, or if the analyzer is more than one year old, additional adjustment and performance verification tests are required to ensure that some newly installed options are functioning properly. However, the completion of these tests does not guarantee that the analyzer meets all warranted specifications.

For more information on accessories go to: www.keysight.com/find/accessories


Related Literature

Keysight CXA signal analyzers

Publication title	Publication number
N9000B CXA X-Series Signal Analyzer, Multi-touch, Data Sheet	5992-1274EN
X-Series Signal Analyzers - Brochure	5992-1316EN
X-Series Measurement Applications, Brochure	5989-8019EN

From Hewlett-Packard through Agilent to Keysight

For more than 75 years, we've been helping you unlock measurement insights. Our unique combination of hardware, software and people can help you reach your next breakthrough. **Unlocking measurement insights since 1939.**



1939

THE FUTURE

myKeysight

myKeysight

www.keysight.com/find/mykeysight

A personalized view into the information most relevant to you.



Three-Year Warranty

www.keysight.com/find/ThreeYearWarranty

Keysight's committed to superior product quality and lower total cost of ownership. Keysight is the only test and measurement company with a three-year warranty standard on all instruments, worldwide. And, we provide a one-year warranty on many accessories, calibration devices, systems and custom products.



Keysight Assurance Plans

www.keysight.com/find/AssurancePlans

Up to ten years of protection and no budgetary surprises to ensure your instruments are operating to specification, so you can rely on accurate measurements.

Keysight Infoline

www.keysight.com/find/service

Keysight Infoline

Keysight's insight to best in class information management. Free access to your Keysight equipment company reports and e-library.

Keysight Channel Partners

www.keysight.com/find/channelpartners

Get the best of both worlds: Keysight's measurement expertise and product breadth, combined with channel partner convenience.

www.keysight.com/find/cxa

For more information on Keysight Technologies' products, applications or services, please contact your local Keysight office. The complete list is available at: www.keysight.com/find/contactus

Americas

Canada	(877) 894 4414
Brazil	55 11 3351 7010
Mexico	001 800 254 2440
United States	(800) 829 4444

Asia Pacific

Australia	1 800 629 485
China	800 810 0189
Hong Kong	800 938 693
India	1 800 11 2626
Japan	0120 (421) 345
Korea	080 769 0800
Malaysia	1 800 888 848
Singapore	1 800 375 8100
Taiwan	0800 047 866
Other AP Countries	(65) 6375 8100

Europe & Middle East

Austria	0800 001122
Belgium	0800 58580
Finland	0800 523252
France	0805 980333
Germany	0800 6270999
Ireland	1800 832700
Israel	1 809 343051
Italy	800 599100
Luxembourg	+32 800 58580
Netherlands	0800 0233200
Russia	8800 5009286
Spain	800 000154
Sweden	0200 882255
Switzerland	0800 805353
	Opt. 1 (DE)
	Opt. 2 (FR)
	Opt. 3 (IT)
United Kingdom	0800 0260637

For other unlisted countries:

www.keysight.com/find/contactus
(BP-01-01-16)



www.keysight.com/go/quality

Keysight Technologies, Inc.
DEKRA Certified ISO 9001:2008
Quality Management System

This information is subject to change without notice.
© Keysight Technologies, 2016
Published in USA, January 28, 2016
5992-1275EN
www.keysight.com