

## TXS-606DT - Microphone Transmitter



**Wireless desktop microphone with integrated multifrequency transmitter, with UHF PLL technology.**

- Electret microphone cartridge, cardioid characteristic
- 350 mm gooseneck, removable
- 1,000 selectable UHF frequencies (672.000-696.975 MHz), can be synchronised with the receivers TXS-606, TXS-626, TXS-646 or TXS-686 via ACT function
- Adjustable sensitivity
- Switchable transmitting power (high: 25 mW/low: 2.5 mW)
- LCD for indicating group/channel, audio level and battery status
- Power supply via 2 x 1.5 V battery AA size (not supplied)

**Licence required for this system in the EU!**

**Please read the notes regarding wireless systems in the section "IMPORTANT INFORMATION"!**

## Technical Data

Type	: desktop microphone
Transmission method	: wireless
Pick-up pattern	: cardioid
System	: electret
Carrier frequency range	: 672.000-696.975 MHz
Transmitting power	: 25 mW/2.5 mW
Power supply	: 2 x 1.5 V batt. AA size
Operating time	: ? 8 h
Audio frequency range	: 30-18,000 Hz, $\pm 3$ dB
Nominal impedance	: -
Sensitivity	: -
S/N ratio	: -
Max. SPL	: -
Power supply	: -
Gooseneck length	:
Housing material	: -
Admiss. ambient temp.	: -
Dimensions	: 120 x 65 x 178 mm (w/o gooseneck)
Weight	: 600 g
Cable	: -
Connection	: -