


## PROLINE G2 PAGODA TOPS



### APPLICATION

Pagoda Tops can be used on the top of a modular enclosure for active cooling. The design features a drip-proof raised pagoda vent with a 115-volt integral axial exhaust fan, and includes gasket seals to maintain a NEMA 12 enclosure rating.

### FEATURES

- Drip-protected, raised pagoda vent
- Integral axial exhaust fan for active cooling

### Standard Product

Catalog Number	W (mm)	W (in.)	D (mm)	D (in.)	Fits Frame WxD
P2TP45	379	14.9	459	18.1	400x500
P2TP46	379	14.9	559	22.0	400x600
P2TP64	579	22.8	359	14.1	600x400
P2TP65	579	22.8	559	22.0	600x500
P2TP66	579	22.8	559	22.0	600x600
P2TP84	779	30.7	359	14.1	800x400
P2TP85	779	30.7	459	18.1	800x500
P2TP86	779	30.7	559	22.0	800x600
P2TP810	779	30.7	959	37.8	800x1000
P2TP104	979	38.5	359	14.1	1000x400
P2TP105	979	38.5	459	18.1	1000x500
P2TP106	979	38.5	559	22.0	1000x600
P2TP124	1179	46.4	359	14.1	1200x400
P2TP125	1179	46.4	459	18.1	1200x500
P2TP126	1179	46.4	559	22.0	1200x600
P2TP128	1179	46.4	759	29.9	1200x800
P2TP164	1579	62.2	359	14.1	1600x400
P2TP165	1579	62.2	459	18.1	1600x500
P2TP166	1579	62.2	559	22.0	1600x600
P2TP168	1579	62.2	759	29.9	1600x800
P2TP185	1779	70.0	459	18.1	1800x500
P2TP186	1779	70.0	559	22.0	1800x600
P2TP188	1779	70.0	759	29.9	1800x800

### SPECIFICATIONS

- 14-gauge (1.75 mm) steel
- Pagoda Tops 1200 mm and greater in width have one drip-protected, raised pagoda vent opening positioned over one side that can be oriented for right or left ventilation
- Maintains NEMA 12 Type rating on enclosure when installed; seamless polyurethane gasket between top and frame (UL component recognized) provides a water-tight, dust-tight seal against moisture and contaminants
- Includes four M12 hex bolts for installation
- Lifting eyes (not included) can be used instead of bolts


### FINISH

- Polyester powder paint; RAL 7035 textured light gray standard
- Custom colors available

### ACCESSORIES

- Lifting eyes
- Pagoda exhaust vent

### BULLETIN: P40



Model	Component	Type	Width	Depth	Specialty	Catalog Number
P2	T	P	8	6	Blank	= P2TP86
PROLINE G2	Top	Blank = solid top P = pagoda top PH = top with cutout for high-performance pagoda vent	mm 18 = 1800 16 = 1600 14 = 1400 12 = 1200 10 = 1000 8 = 800 6 = 600 4 = 400	mm 10 = 1000 8 = 800 6 = 600 5 = 500 4 = 400	Blank = standard HF = EMC protected	

PROLINE G2 PAGODA EXHAUST VENTS



APPLICATION

PROLINE G2 Pagoda Exhaust Vents can be field-installed on any PROLINE G2 solid top to provide active enclosure cooling.

FEATURES

- Axial fan and finger guard mounted in housing
- Drip-protected raised cover is removable from the inside of the enclosure

PROLINE G2 HIGH-PERFORMANCE PAGODA EXHAUST VENT



APPLICATION

The PROLINE G2 High-Performance Pagoda Exhaust Vent can be installed on any PROLINE G2 solid top.

FEATURES

- Integral centrifugal blower mounted in a protective housing
- Can be installed on any PROLINE G2 solid top

SPECIFICATIONS

- 14-gauge (1.75 mm) steel
- 115V or 230V versions with lead wires
- 115V power cord option
- Rated UL Type 1; installing this component on an enclosure brings the enclosure rating to UL Type 1
- Includes gasket and mounting hardware

FINISH

- Polyester powder paint; RAL 7035 textured light gray standard
- Custom colors available

BULLETIN: P20

Standard Product

Catalog Number	Description
PPT1	LEADWIRE 115V,50/60Hz
PPT2	LEADWIRE 230V,60Hz

SPECIFICATIONS

- Drip-protected raised cover is removable from the inside of the enclosure
- Housing includes a drip-proof removable hood, wire mesh finger guard and perimeter gasket
- Lead wire or power cord options
- 115V or 230V versions
- Rated UL Type 1; installing this component on an enclosure brings the enclosure rating to UL Type 1
- Installation hardware is included

FINISH

- Polyester powder paint; RAL 7035 textured light gray standard
- Custom colors available

BULLETIN: P20

Standard Product

Catalog Number	Description
PPTHP1	LEADWIRE 115V,60Hz
PPTHP2	LEADWIRE 230V,60Hz

## PROLINE G2 TOP WITH CUTOUT FOR HIGH-PERFORMANCE PAGODA EXHAUST VENT



### APPLICATION

The PROLINE G2 Top Cutout for High Performance Pagoda Exhaust Vents have cutouts that accept one high-performance pagoda vent.

### SPECIFICATIONS

- Top with cutout for High Performance Pagoda Exhaust Vents
- A High Performance Pagoda Exhaust Vent can be used with any PROLINE G2 solid top by requesting a cut-out modification
- Bolts are furnished to hold top in position (lifting eyes can be used in place of bolts)
- Seamless polyurethane gasket between top and frame (UL component recognized) provides a water-tight, dust-tight seal against moisture and contaminants
- Ground studs are included


### FINISH

- Polyester powder paint; RAL 7035 textured light gray standard
- Custom colors available

### BULLETIN: P40

Standard Product

Catalog Number	Nominal W mm/in.	Nominal D mm/in.
P2TPH66	600 23.62	600 23.62
P2TPH68	600 23.62	800 31.50
P2TPH86	800 31.50	600 23.62
P2TPH88	800 31.50	800 31.50



Notes