



All Categories ▼

0 item(s) | \$0.00

Products Standards and Compliance Customer Support Technical Support

Home > TSDDetails

Close | [Print TDS](#)



Technical Data Sheet

BRADY B-593 RAISED PANEL LABEL

TDS No. B-593

Effective Date: 07/09/2010

Description:

GENERAL

Print Technology: Thermal Transfer

Material Type: Polyester

Finish: White, Black, Yellow, Metallized, Red, Green

Adhesive: Permanent Acrylic, Foam Backed

APPLICATIONS

B-593 Raised Panel labels are designed for patch panel identification in identifying external push-buttons, switches, and internal connection points. B-593 is also used as rating and serial plates using alphanumerics that require name plate quality.

RECOMMENDED RIBBONS

Brady Series R6000

Brady Series R6000HF (low halogen)

Brady Series R4400 white

REGULATORY/AGENCY APPROVALS

UL: B-593 (white, metallized, yellow, red and green) is a UL Recognized Component when printed with the Brady R6000 Series and R6000HF Series black ribbons. B-593 (red, green and black) is a UL Recognized Component when printed with the Brady R4400 Series white ribbon. See UL file PGJ12.MH17154 for specific details. UL information can be accessed on line at *UL.com*. Search in *Certifications* area.

cUL: B-593 (white, metallized, yellow, red and green) is a cUL Recognized Component when printed with the Brady R6000 Series black ribbon. B-593 (red, green and black) is a cUL Recognized Component when printed with the Brady R4400 Series white ribbon. See UL file PGJ18.MH17154 for specific details. UL information can be accessed on line at *UL.com*. Search in *Certifications* area.

Brady B-593 is RoHS compliant to 2005/618/EC MCV amendment to RoHS Directive 2002/95/EC.

SPECIAL FEATURES

Brady B-593 Raised Panel Labels have been found to be functional for the following outdoor durations based on long term accelerated weathering tests:

| Brady B-593 Label Color/Ribbon | Estimated Outdoor Durability |
|--------------------------------|------------------------------|
| | |

| | |
|--------------------|----------|
| White/R6000 Black | 10 years |
| Yellow/R6000 Black | 5 years |
| Silver/R6000 Black | 5 years |
| Green/R6000 Black | 5 years |
| Red/R6000 Black | 5 years |
| Red/R4400 White | 3 years |
| Black/R4400 White | 3 years |
| Green/R4400 White | 3 years |

Details regarding label and print appearance are given in the Performance Properties - Environmental section below.

Details:

| PHYSICAL PROPERTIES | TEST METHODS | AVERAGE RESULTS |
|---|--|---|
| Thickness | ASTMD 1000 - Substrate - Foam backed adhesive - Total | 0.0079 inch (0.200 mm) 0.0177 inch (0.450 mm) 0.0256 inch (0.650 mm) |
| Adhesion to: - Stainless Steel - Smooth ABS - Powdercoated surface - Polyethylene | ASTMD 1000 20 minute dwell 24 hour dwell 20 minute dwell 24 hour dwell 20 minute dwell 24 hour dwell 20 minute dwell 24 hour dwell | 32 oz/inch (35 N/100 mm) 90 oz/inch (98 N/100 mm) 88 oz/inch (96 N/100mm) 134 oz/inch (147 N/100 mm) 109 oz/inch (120 N/100mm) 166 oz/inch (182 N/100 mm) 130 oz/inch (142 N/100mm) > 200 oz/inch (> 200 N/100 mm) |
| Drop Shear | PSTC-7 (except use 1/2" x 1" sample) | 35 hours |
| Tack | ASTMD2979 Polyken™ Probe Tack (1 second dwell) | 16.5 oz (469 g) |

| | |
|-------------------------------|----------------------|
| PERFORMANCE PROPERTIES | ENVIRONMENTAL |
|-------------------------------|----------------------|

B-593 white, silver, yellow, red and green label samples were printed with the R6000 Series and R6000HF Series ribbons and B-593 black, red and green label samples were printed with the R4400W series ribbon and dwelled for 24 hours prior to test.

| PERFORMANCE PROPERTIES | TEST METHODS | TYPICAL RESULTS White B-593/R-6000 and B-593/R6000HF | TYPICAL RESULTS Black B-593/R- 4400W | TYPICAL RESULTS Metallized B-593/R- 6000 |
|--------------------------|--|--|--|--|
| High Service Temperature | 1000 hours at 100°C (212°F) | No visible effect | No visible effect | No visible effect |
| Low Service Temperature | 1000 hours at -20°C (-4°F) | No visible effect | No visible effect | No visible effect |
| Humidity Resistance | 1000 hours at 37°C (100°F), 95% R.H. | No visible effect | No visible effect | No visible effect |
| Salt fog | 1000 hours at 5% Salt Spray | No visible effect | No visible effect | No visible effect |
| Abrasion Resistance | Taber Abraser, CS-10 wheels, 500 g/arm (Fed. Std. 191A, Method 5306) | Number of cycles until print is illegible 175 cycles | Number of cycles until print is illegible 75 cycles | Numbers of cycles until print is illegible 175 cycles |

Brady B-593 labels underwent accelerated weathering testing (ASTM G155, Cycle 1) over the course of one year.

Observations regarding the appearance of the B-593 labels and print on the labels were made at 4 intervals during the one year and are given in the table below.

| Weatherometer Duration | Label Color | Effect to Label and Print | | |
|------------------------|-------------|---------------------------|--|----------------------------------|
| | | Effect to Label Color | Effect To R6000 Series Printing | Effect to R4400W Series Printing |
| 1000 hours | White | No visible effect | No visible effect for all label colors. n/a | n/a |
| | Red | Slight discoloration | | No visible effect |
| | Green | Slight discoloration | | No visible effect |
| | Yellow | No visible effect | | n/a |
| | Silver | No visible effect | | n/a |
| | Black | No visible effect | | No visible effect |
| 2400 hours | White | No visible effect | No visible effect | n/a |
| | Red | Severe discoloration, | Slight print fade | Slight print fade |

| | | | | |
|------------|--------|--|-------------------|--|
| | Green | retains a trace of red | No visible effect | No visible effect |
| | Yellow | Moderate discoloration | No visible effect | n/a |
| | Silver | Slight discoloration | No visible effect | n/a |
| | Black | Slight discoloration Slight loss of gloss | n/a | no visible effect |
| 4800 hours | White | No visible effect | No visible effect | n/a |
| | Red | Severe discoloration, retains a trace of red | Slight print fade | slight print discoloration |
| | Green | Moderate discoloration | No visible effect | slight print discoloration |
| | Yellow | Slight discoloration | No visible effect | n/a |
| | Silver | Moderate discoloration | No visible effect | n/a |
| | Black | Slight loss of gloss | n/a | no visible effect |
| 9100 hours | White | Slight discoloration | No visible effect | n/a |
| | Red | Severe discoloration, retains a trace of red | Slight print fade | Severe print removal, print is barely legible* |
| | Green | Moderate discoloration | Slight print fade | Severe print removal, print is barely legible* |
| | Yellow | Moderate discoloration | Slight print fade | Severe print removal, print is barely legible* |
| | Silver | Severe discoloration | Slight print fade | n/a |
| | Black | Slight loss of gloss | n/a | n/a |
| | | | | no visible effect |

Based on internal testing results, 800 hours in the Weatherometer is *approximately* equivalent to one year of outdoor exposure in Wisconsin.

*print can be rubbed off with finger

| | |
|-----------------------------|----------------------------|
| PERFORMANCE PROPERTY | CHEMICAL RESISTANCE |
|-----------------------------|----------------------------|

B-593 white printed with the R6000 Series and R6000HF Series ribbons and B-593 black printed with the R4400 white series ribbon, and dwelled 24 hours prior to test. Testing consisted of 5 cycles of 10 minute immersions in the specified chemical reagent followed by 30 minute recovery periods. After final immersion, samples rubbed 10 times with cotton swab saturated with test fluid.

| CHEMICAL REAGENT | SUBJECTIVE OBSERVATION OF VISUAL CHANGE - B-593 White | | | |
|-------------------|---|----------|-------------|----------|
| | EFFECTS TO THE PRINTED IMAGE | | | |
| | R6000 | | R6000HF | |
| | Without Rub | With Rub | Without Rub | With Rub |
| Isopropyl alcohol | 1 | 1 | 1 | 1 |

| | | | | |
|----------------------------|----|----|----------------|-----|
| Methyl ethyl ketone | NP | NP | 1 | 5 |
| Alcohol mix* | 1 | 1 | 1 | 1 |
| Gasoline | 1 | 5 | 1 | 1 |
| Diesel | 1 | 1 | 1 | 1 |
| Skydrol® 500B-4 | 1 | 5 | 1 | 2-3 |
| Mil 5606 Oil | 1 | 1 | 1 | 1 |
| 1,1,1-Trichloroethane | 1 | 5 | Fluid obsolete | |
| 5% Sodium hydroxide | 1 | 1 | 1 | 1 |
| 10% Sulfuric acid solution | 1 | 1 | 1 | 1 |
| Deionized water | 1 | 1 | 1 | 1 |
| 10% Salt water solution | 1 | 1 | 1 | 1 |
| n-Hexane | 1 | 1 | Not tested | |
| Iso-octane | 1 | 1 | Not tested | |
| Ethanol | 1 | 1 | 1 | 1 |
| ASTM #3 oil | 1 | 1 | 1 | 1 |
| Acetone | 1 | 5 | 1 | 5 |

* Alcohol mix is 50% ethanol, 30% methanol, and 20% water by volume.

| CHEMICAL REAGENT | SUBJECTIVE OBSERVATION OF VISUAL CHANGE – B-593 Black | |
|---------------------|---|----------|
| | EFFECTS TO THE PRINTED IMAGE | |
| | R4400W | |
| | Without Rub | With Rub |
| Isopropyl alcohol | 1 | 5 |
| Methyl ethyl ketone | NP | NP |

| | | |
|----------------------------|----|----|
| Alcohol mix* | 1 | 1 |
| Gasoline | 1 | 5 |
| Diesel | 1 | 1 |
| Skydrol® 500B-4 | NP | NP |
| Mil 5606 Oil | 1 | 1 |
| 1,1,1-Trichloroethane | 1 | 5 |
| 5% Sodium hydroxide | 1 | 1 |
| 10% Sulfuric acid solution | 1 | 1 |
| Deionized water | 1 | 1 |
| 10% Salt water solution | 1 | 1 |
| n-Hexane | 1 | 1 |
| Iso-octane | 1 | 1 |
| Ethanol | 1 | 4 |
| ASTM #3 oil | 1 | 4 |
| Acetone | NP | NP |

* Alcohol mix is 50% ethanol, 30% methanol, and 20% water by volume.

Rating Scale:

1=no visible effect

2=slight print smear, fade or removal

3=moderate smear, fade or print removal (print is still legible)

4=severe smear, fade or print removal

5=complete print and/or topcoat removal

NP=print removed during immersion

Product testing and history of similar products, support a customer performance expectation of at least **two years from**

the date of receipt for this product as long as this product is stored in its original packaging in an environment below

80°F (27°C) and 60% RH. We are confident that our product will perform well beyond this time frame. However,

it remains the responsibility of the user to assess the risk of using such product. We encourage customers to

develop functional testing protocols that will qualify a product's fitness for use, in their actual application.

Trademarks:

Polyken™ is a trademark of Testing Machines Inc.
Skydrol® is a registered trademark of the Monsanto Company
ASTM: American Association for Testing and Materials (U.S.A.)
S. I.: International System of Units

Note: All values shown are averages and should not be used for specification purposes.

Test data and test results contained in this document are for general information only and shall not be relied upon by Brady customers for designs and specifications, or be relied on as meeting specified performance criteria. Customers desiring to develop specifications or performance criteria for specific product applications should contact Brady for further information.

Product compliance information is based upon information provided by suppliers of the raw materials used by Brady to manufacture this product or based on results of testing using recognized analytical methods performed by a third party, independent laboratory. As such, Brady makes no independent representations or warranties, express or implied, and assumes no liability in connection with the use of this information.

WARRANTY

Brady products are sold with the understanding that the buyers will test them in actual use and determine for themselves their adaptability to their intended uses. Brady warrants to the buyers that its products are free from defects in material and workmanship, but limits its obligation under this warranty to replacement of the product shown to Brady's satisfaction to have been defective at the time Brady sold it. This warranty does not extend to any persons obtaining the product from the buyers. This warranty is in lieu of any other warranty, express or implied, including, but not limited to, any implied warranty of merchantability or fitness for a particular purpose, and of any other obligations or liability on Brady's part. Under no circumstances will Brady be liable for any loss, damage, expense, or consequential damages of any kind arising in connection with the use, or inability to use, Brady's products.

Copyright 2015 Brady Worldwide, Inc. | All Rights Reserved
Material may not be reproduced or distributed in any form without written permission.

Brady North America | 6555 W. Good Hope Rd | Milwaukee, WI 53223 | USA | Tel: 414-358-6600 | Fax: 800-292-2289

CONTACT

Contact Us
Email Subscription
International Sites

ABOUT

Company Information
News & Events

CORPORATE INFORMATION

Privacy Policy
Terms of Use

SOCIAL

Facebook
Twitter
YouTube

©2016 Brady Worldwide, Inc

[Mobile](#) [Sitemap](#)



Brady identifies and protects products, people, and premises with high performance labels, industrial label printers, software, safety & facility identification, spill control, Lockout Tagout solutions and more. Brady helps you create and maintain safer work environments and comply with regulatory standards. Our high-performance materials clearly identify products, components and other assets, even in the most extreme conditions.