

**SSB-1900/NB**Drop Ceiling Adjustable Load Support,  
without 1900 Box**GENERAL DESCRIPTION**

The SSB-1900/NB is a rust resistant steel, adjustable, load bearing support without an electrical junction box.

**INTENDED USE - Indoor or Protected Outdoor Environment**



<b>Installation</b>	Parallel to floor plane in a suspended ceiling structure; maximum span of 24" in one dimension.
---------------------	---

**JUNCTION BOX ACCESS**

<b>All 4 Vertical Sides</b>	2x 1/2" k/o conduit 1x 1/2" / 3/4" eccentric k/o conduit
<b>Top Horizontal Surface</b>	3 x 1/2" k/o conduit 2x 1/2" / 3/4" eccentric k/o conduit

**MECHANICAL ATTACHMENT**

<b>Bottom Horizontal</b>	2x 8-32 formed threads to attach 2-gang Surface adapter plate if required
<b>Tie-Offs</b>	4x Total, 1 each at end of bridge rail 2x Terminal plate



Recommended construction sequences, installation instructions, and A&E Specifications are available in various formats in the QUAM Architects' and Engineers' Resources section on the web at:  
[www.QuamSpeakers.com](http://www.QuamSpeakers.com)

© 2013 Quam-Nichols Company reserves the right to make changes and/or improvements to its products at any time and without notice.



QUAM-NICHOLS COMPANY, INC.  
234 East Marquette Rd.  
Chicago, IL. 60637  
Tel: 1-800-NEED-NOW (800-633-3669)  
Fax: 1-888-NEED-NOW (888-633-3669)  
e-mail: [NeedNow@QNC.com](mailto:NeedNow@QNC.com)  
[www.QuamSpeakers.com](http://www.QuamSpeakers.com)