## **SERIES 62SG**

## **Compact / Cost Effective**

### **FEATURES**


- Just 0.3-inch behind panel depth
- Over 1 million rotational cycles
- 2-bit gray code output
- · Quadrature coding
- Available in 16, 24 and 32 detent positions
- Optional integrated pushbutton
- · Light pipe technology
- Cost competitive with mechanical encoders at higher volumes

### **APPLICATIONS**

- · Automotive
  - audio systems
  - navigation systems
- Medical
  - patient monitoring systems
- Test & Measurement
  - analyzers
  - oscilloscopes
- · Audio & Video
  - consumer electronics
  - professional editing equipment




## **DIMENSIONS** in inches (and millimeters)





#### **WAVEFORM AND TRUTH TABLE**



#### **SPECIFICATIONS**

#### **Environmental Specifications**

Operating Temperature: -40°C to 85°C Storage Temperature: -40°C to 85°C Humidity: 96 hours@90-95% humidity@40°C Mechanical Vibration: Harmonic motion with amplitude of 15g within a varied frequency of 10 to 2000 Hz for 12 hours Mechanical Shock:

**Test 1:** 100g for 6 ms half-sine wave with a velocity change of 12.3 ft/s.

**Test 2:** 100g for 6 ms sawtooth wave with a velocity change of 9.7 ft/s.

# Rotary Electrical and Mechanical Specifications

Operating Voltage:  $5.00\pm0.25~\text{Vdc}$  Supply Current: 30~mA maximum Logic Output Characteristics: Logic high: no less than 3.0~Vdc Logic low: no greater than 1.0~Vdc Output: Open Collector Phototransistor Optical Rise Time: 30~ms maximum Optical Fall Time: 30~ms maximum

AVERAGE ROTATIONAL TORQUE SPECIFICATIONS			
	LOW	MEDIUM	HIGH
	±0.50 IN-OZ	±1.40 IN-OZ	±1.60 IN-OZ
16 POSITION	1.40	2.35	3.40
24 POSITION	1.25	1.95	2.95
32 POSITION	0.95	1.40	2.15

50% of initial value after 1 million cycles.

**Mechanical Life:** 1,000,000 cycles of operation. 1 cycle is a rotation through all positions and a full return

Mounting Torque: 15in-lbs. maximum Shaft Pushout Force: 45 lbs. minimum Terminal Strength: 15 lbs. cable pull out

force minimum

Solderability: 95% free of pin holes & voids

# **Pushbutton Electrical and Mechanical Specifications**

Rating: 30 mA @ 5 Vdc

Contact Resistance: <10  $\Omega$  (Compatible

with CMOS or TTL)

Life: 1 million actuations minimum

Contact Bounce: <4 ms make, <10ms break Actuation Force: 5 = 510 ± 150 grams

Actuation Force: 5 = 510 ± 150 gran

 $9 = 950 \pm 150 \text{ grams}$ **Shaft Travel:** .017 ± .008 inch

## **Materials and Finishes**

Bushing: Zamak 2 Shaft: Zamak 2

Detent Ball: 302 Stainless Steel
Detent Spring: Music Wire
Retaining Ring: 301 Stainless Steel

Code Housing: Nylon 6/6 25% glass

reinforced. Zytel FR-50 **Light Pipe:** Lexan, GE **Code Rotor:** Delrin 100

Pushbutton Actuator: Glass Reinforced nylon 6/6. Zytel 70G33L. UL 94 Pushbutton Dome: 301 Stainless Steel Printed Circuit Board: NEMA Grade FR4, Double clad with copper, Plated with gold

over nickel

Infrared Emitting Diode: Gallium Aluminum

Arsenide

Phototransistor Diode: NPN Silicon Resistor: Metal oxide on ceramic substrate

Spacer: Pet plastic

Backplate: 302 Stainless Steel Label: TT406 thermal transfer cast film Solder: 96.5% tin / 3% silver / 0.5% copper.

No clean

Hex Nut: Brass, Plated with nickel

Lockwasher: Zinc Plated Spring Steel with

Clear Trivalent Chromate Finish

Cable: Copper Stranded with topcoat in PVC

insulation

Connector (.050 center): PA4.6 with tin/

nickel plated phosphor bronze.

